


# DIP SWITCH NDA SERIES

## Right Angle Type



### FEATURES

- ※ Side actuation
- ※ Gold contact for high reliability
- ※ Red, blue, and black color options.


### APPLICATION

- ※ Industrial control
- ※ Computers and peripherals
- ※ Variety of function controls

### SPECIFICATION

|                       |                    |
|-----------------------|--------------------|
| Contact Rating        | 25mA, 24V DC       |
| Contact Resistance    | 50mΩ max.          |
| Insulation Resistance | 100MΩ min. 500V DC |
| Dielectric Strength   | 500V AC/1 minute   |
| Operating Force       | 1,000gf max.       |
| Travel                | 2mm                |
| Operating Life        | 2, 000 cycles      |
| Operating Temp.       | -40°C ~ +85°C      |
| Storage Temp.         | -40°C ~ +85°C      |

### CIRCUIT




### PACKAGE




#### <Tube>

|               |                 |
|---------------|-----------------|
| NDA-02: 73pcs | NDA-02T: 70 pcs |
| NDA-03: 52pcs | NDA-03T: 50 pcs |
| NDA-04: 40pcs | NDA-04T: 39 pcs |
| NDA-05: 33pcs | NDA-05T: 32 pcs |
| NDA-06: 28pcs | NDA-06T: 28 pcs |
| NDA-07: 24pcs | NDA-07T: 24 pcs |
| NDA-08: 21pcs | NDA-08T: 21 pcs |
| NDA-09: 19pcs | NDA-09T: 19 pcs |
| NDA-10: 17pcs | NDA-10T: 17 pcs |
| NDA-12: 14pcs | NDA-12T: 14 pcs |

### HOW TO ORDER



## NDA



| PART NO. | NO.OF POS. | DIM.A | DIM.B |
|----------|------------|-------|-------|
| NDA-02   | 2          | 6.44  | 2.54  |
| NDA-03   | 3          | 8.98  | 5.08  |
| NDA-04   | 4          | 11.52 | 7.62  |
| NDA-05   | 5          | 14.06 | 10.16 |
| NDA-06   | 6          | 16.60 | 12.70 |
| NDA-07   | 7          | 19.14 | 15.24 |
| NDA-08   | 8          | 21.68 | 17.78 |
| NDA-09   | 9          | 24.22 | 20.32 |
| NDA-10   | 10         | 26.76 | 22.86 |
| NDA-12   | 12         | 31.84 | 27.94 |

