


Part Number : [2124150200](#)

Product Description : 2.50mm Pitch, Board-In
Crimp Housing, 2 Circuits, Right-Angle, Natural

Series Number : 212415

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2124150200_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2124150000PK-000.pdf](#)

[2124150000PS-000.pdf](#)

Tooling Specifications

[350210000CS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	212415
Description	2.50mm Pitch, Board-In Crimp Housing, 2 Circuits, Right-Angle, Natural
Application	Wire-to-Board
Component Type	Housing
Product Name	Board-in
UPC	193264513635

Physical

Circuits (maximum)	2
Color - Resin	Natural
Gender	N/A
Glow-Wire Capable	No
Material - Resin	Polyamide (PA)
Net Weight	0.062/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Use with Part(s)

Description	Part Number
2.00/2.50mm Pitch, Board-in Crimp Terminal, Male, Right-Angle, Brass Pre-Plated Tin, 28-22 AWG, Reel	<u>350211001</u>
2.00/2.50mm Pitch, Board-in Crimp Terminal, Male, Right-Angle, Phosphor Bronze Post-Plated Tin, 28-22 AWG, Reel	<u>350211160</u>

This document was generated on Sep 07, 2026