

0481.500 - 481 Series



Series: 481 Series

Questions? [Contact Littelfuse Support](#)

 [481 Series Datasheet](#)

- Color-coded indicator flags indicate ampere rating.
- Body is constructed of black polyphenylene sulfide with UL-94V0 flammability rating, contacts are of bright alloy-plated beryllium copper.
- Ideal for telecommunications and control panel circuits.
- Eliminates down time by immediately pinpointing the blown (open) circuit while triggering LED or audio alarm, while placed in mating holder (482 Series).
- Clear plastic lens option available for additional safety.

 [Check Stock](#)

 [Order Samples](#)

Product Literature

 [481 Series Data Sheet](#)

 [481 Series Time Curve](#)

Feedback

Electrical Characteristics	
Technical Resources	
Property (Mouseover for details)	Value
Ampere Rating (A)	0.5
Nominal Melting I ² T (A ² sec)	0.49
Interrupting Rating	300A@125VAC
Nominal Cold Resistance (Ohms)	1.52
Opening	Fast-Acting (F)
VAC (V)	125

Connect with Littelfuse

Sign up to receive special offers and news

Enter your email

Submit

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

About Littelfuse

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

Explore Littelfuse

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

Technical Resources

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents