

Image coming soon

Part Number : [1301120158](#)
Product Description : Incandescent Stringlight
Construction Guard 1-1/2 Neck Zinc Plated, Long,
Narrow Profile
Series Number : 130112
Status : Obsolete
Product Category : Portable Lighting Accessories
Engineering Part Number : 368

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Portable Lighting Accessories
Series	130112
Description	Incandescent Stringlight Construction Guard 1-1/2 Neck Zinc Plated, Long, Narrow Profile
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78678861168

Electrical

Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Commercial
Guard Included	Yes
Guard Type	Steel
Height	241.30mm (9.500")
Lamp Type	PS30
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Outlet	N/A
Packaging Type	Carton

This document was generated on Sep 07, 2026