



Products

Customize Your Parts

Industries Solutions

Search

News & Events

First Time?



(0)



Home / Products / X-Lok / Accessory

Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

Accessory

Middle Size

Mini Size

Large Size

Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

CC1 >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



AB-AD-040404-FFM-TQ001

Operating Temperature: -20°C ~ +85°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: PVC

Certificate: N/A

You must login first for view the price

Quantity - 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Specifications

Download / CAD

Nominal Current

5A

Connector Type

T Adaptor

Shielded

Plastic, Non-shielded

No. of Contacts

04

Connector Gender

Female

Backshell

N/A

Mating Style

Push Lock

IP Rating

IP69K

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >

Assembly Style

N/A

More Options

People Also Bought

