

CS8365C



50 Amp, 250 Volt, Black & White Locking Plug, Industrial Grade

50 Amp, 3-Phase 250V AC, Non-NEMA, 3P, 4W, Black & White Locking Plug, Industrial Grade, Grounding, California-Style(CS)-BLACK-WHITE

- Captive, quick drive assembly screws for faster assembly
- Unique cord clamp accepts wide range of cord sizes
- Rugged nylon construction resists impact, heat, chemicals, and rough use
- Industry exclusive limited lifetime warranty

Technical Information

UPC Code : 078477326381

Country Of Origin : Mexico

NEMA : Non-NEMA

Environmental Specifications

Environment : Dry

Flammability : UL94 V-2

Operating Temperature : -40° C to 75°C

Material Specifications

Assembly Screws : Brass

Cable Clamp Screw : Philips Head, SS 304

Color : Black-White

Compression Nut, Strain Relief : Nylon

Connector Contact - Spring : 0.041-inch thick Brass

Contact - Binding Plate : 0.100-inch thick Brass

Contact Rivet : Brass

Dust Shield : Santoprene TPE

Face Module : Nylon

Grommet/Gasket : Santoprene TPE

Ground Post : Brass

Ground Shunt : Bronze

Housing : Nylon

Housing Material : Nylon

Plug Blade : 0.1000-inch thick Brass

Plug Blade Shroud : SS 302 /304

Standard Cable Clamp : Nylon

Terminal Block : 0.062-inch thick Copper

Terminal Set Screw : SS 302 /304

Wiring Chamber : Nylon

Mechanical Specifications

Product Features

Amperage : 50 A
Brand : Black and White
Cord Range : .680 - 1.125
Color : Black-White
Current Interrupting : Certified for current interrupting at full rated current
Device Type : Locking Plug
NEMA : Non-NEMA
Dielectric Voltage Withstand : 2000V minimum per UL 498
Grounding : Grounding
Maximum Working Voltage : 3-Phase 250V as rated
Phase : 3-Phase
Pole : 3
Product ID : Ratings and Catalogue No. molded into face and stamped into shroud
Temperature Rise : Max 30°C temp rise at full-rated current after 150 cycles of OL at 150% rated DC current
Terminal Accom. : AWG #10 to #4 Stranded Wire
Terminal ID : X, W, Y, Z and Green for ground
Torque Range : 20-30 in-lbs
Voltage : 250 VAC
Wire : 4

Standards and Certifications

CSA C22.2 No. 42 : File 152105


NOM : 057

RoHS : Compliant

UL 498 : File E13399

Warranty : Limited Lifetime Warranty

Dimensional Drawing



SPECIFICATION SUBMITTAL

JOB NAME: JOB NUMBER:	CATALOG NUMBERS: <table border="1"> <tr> <td> </td> <td> </td> </tr> <tr> <td> </td> <td> </td> </tr> </table>				

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.

T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-461-2002 ·

FAX: +1-800-824-3005 ·

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)

5386- 1797 ·

Visit our Website at: www.leviton.com

© 2026 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/company/about-leviton/locations

© 2026 Leviton Manufacturing Co., Inc.