






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A	Initial Release	2015/07/14	Mafei	Change Rev.01 To Rev.A




CB-XXBMMC-RL7001	Without Cable
	IP67
	Straight(180°)
	Snap in with Latch(彈臂卡合)
	Crimp Type(鉗接式)
	Male Pin(公Pin)
	Male Connector(公座)
	For Cable without SR(無網尾)
	No. Of Pin(Pin 數)
	Middle Size Current Rating 10A

Note:


- * Important Dimension To Check.
- * Waterproof Rate: IP67 (Mating)
- * Housing: M-PPE, Black, UL94 V-0, UL746C fl
- * Conductor Current Rating: Max.10A Depends On Wire
- * O-Ring: Silicone, Gray, UL94 V-0
- * Seals: Silicone, Gray, UL94 V-0
- * Clamp Ring: Nylon, Black, UL94 V-0, UL746C fl
- * Sealing Nut: Nylon, Black, UL94 V-0, UL746C fl
- * Seal 1 For Cable OD: $\varnothing 4.5\text{mm} \sim \varnothing 7.5\text{mm}$
- * Seal 2 For Cable OD: $\varnothing 7.5\text{mm} \sim \varnothing 9.5\text{mm}$
- * Prohibiting the use of place in oils.
- * Clamp Ring Recommended Tightening Torque: 4~7 Kgf.cm(0.4~0.7 N.m)
- * Sealing Nut Recommended Tightening Torque: 5~10 Kgf.cm(0.5~1 N.m)



Pin2
Pin Assignments
Front View



Pin3
Pin Assignments
Front View





Pin4
Pin Assignments
Front View


UNIT:mm		TITLE
TOLERANCE		ASSY RBL 10A M CONN M PIN
±0.5		SCALE 1:1 SIZE A4 SHEET 1 OF 2
REV. A	WC-REV. A.2	Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Mafei	2015-07-14
CUSTOMER	Alex_Lin	DATE
ALTW	Jerry	2015-07-14



QTY: XX Pcs



UNIT:mm				TITLE	
				ASSY RBL 10A M CONN M PIN	
TOLERANCE		SCALE	SIZE	SHEET	
.X	±0.25	1:1	A4	2	OF 2
.XX	±0.1				
.XXX	±0.05				
ANGLES	±1°	REV.	WC-REV.		
		A	A.2	CC: Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Mafe i	2015/07/14
DWG NO	CHECKED BY	DATE
CB-XXBMMC-RL7001	Alex_Lin	2015/07/14
CUSTOMER	APPROVED BY	DATE
ALTW	Jerry	2015/07/14