


8 7 6 5 4 3 2 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

MODEL NUMBER	LENGTH	
	FEET	METERS
CGDVI-DL-MM-1	1.0	[.31]
CGDVI-DL-MM-3	3.0	[.92]
CGDVI-DL-MM-5	5.0	[1.52]
CGDVI-DL-MM-10	10.0	[3.05]
CGDVI-DL-MM-15	15.0	[4.57]


REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/16/12	D. GRIFFIN
B	ECN 6159: CHANGED MOLDED HOODS, FERRITES, AND BULK CABLE TO BLACK	5/10/12	D. DESJARDIN



NOTES:

1. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLIES SHALL BE INDIVIDUALLY PACKAGED IN A CLEAR POLYBAG AND LABELED PER LSP-010
3. DUST COVERS INSTALLED FOR SHIPPING (NOT SHOWN).

RoHS Compliant

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: 012 [305] = +1 [25] / -0 >12 [305] 060 [1524] = +2 [51] / -0 >60 [1524] 0120 [3048] = +4 [102] / -0 >120 [3048] 0300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = N .2 .XX = N .02 .XXX = N .005	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. DESJARDIN	4/13/12		
	CHECKED BY R. SCOTT	4/16/12	CATEGORY VIDEO	
	APPROVED BY S. SMITH	4/16/12	PRODUCT DESCRIPTION CA DVI-D M/M DUAL LNK	
PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		SIZE A	FSCM NO. 43321
COLOR VARIATIONS MAY OCCUR		DWG. NO. CGDVI-DL-MM	REV. B	SCALE: NONE
		CAD FILE: CGDVI-DL-MM.SLDDRW	SHEET 1 OF 1	