

Home // Industrial // signal|mate® C091 - M16 Circular Connectors // M16-D Circular Connectors // C091 31N003 100 2 U



C091 31N003 100 2 U

Description	Female panel connector 3 pole IP67; solder; silver; screw locking
IP-class mated	IP69k
number of positions (w/o PE)	3
rated current (40 °C)	10 (A)
rated voltage	300 (V)

● active

Please log in to receive your price.

The minimum order amount is 50 pcs.;
packing unit 50 pcs.
This product is currently not in stock.

add to cart

add to favorite

send request

Technical data

Downloads

General Characteristics

contact diameter	1,5 mm
gender	female
IP-class mated	IP69k
locking system	screw coupling
number of positions (w/o PE)	3
part category	female receptacle
termination	solder pin

Further Characteristics

max. wire gauge	0.5
min. wire gauge	0.05
RoHS Compliant Yes	X

Electrical Characteristics

rated current (40 °C)	(A)	10
rated voltage	(V)	300

Compatible accessory



Matching contacts



Last viewed



HVPTB3N50
HVPTB 3 Pole, 50mm², N coded



HVCOCF6ATR8SF970L0000
Female panel connector; 8 pole; CCS2 - 200.



C146 10B008 902 15
Female module; 8 pole; Crimp



C091 11N003 000 2 U
Female panel connector 3 pole IP67; crimp;

News and Events

Please visit us on the coming shows and find out more information about our new products.
[Read more](#)

Downloads

Click here to download our product catalogues and additional information. [Read more](#)

About us

Amphenol Tuchel Industrial GmbH is a division of the US-based Amphenol Corporation. With more than 90 000 employees the organisation belongs to the leading manufacturers of electrical, electronic and fiber optic connectors worldwide. [Read more](#)