


Data Sheet | Item Number: 281-418

Test plug module; modular; suitable for all WAGO 281, 776, 777 and 781 series rail-mounted terminal blocks with jumper slots in the current bar; gray

<https://www.wago.com/281-418>



Color: ■ gray

Notes	
Safety Information	These test plugs are not suitable for Ex e applications.

Electrical data	
General information	
Test voltage	400 V
Test current	6 A

Physical data	
Width	6 mm / 0.236 inches
Module width	6 mm / 0.236 inches

Material data	
Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.02 MJ
Weight	1.9 g



Commercial data	
Product Group	1 (Rail Mounted Terminal Blocks)
PU (SPU)	100 (25) pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918276320
Customs tariff number	85366990990

Product Classification	
UNSPSC	39121410
eCl@ss 10.0	27-14-11-48
eCl@ss 9.0	27-14-11-48
ETIM 9.0	EC002255
ETIM 10.0	EC002255
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 281-418

↓

Documentation			
Bid Text			
281-418	19.02.2019	xml 2.88 KB	↓
281-418	28.04.2017	doc 23.50 KB	↓

CAD/CAE-Data	
CAD data 2D/3D Models 281-418 ↓	CAE data WSCAD Universe 281-418 ↓


1 Compatible Products
1.1 Optional Accessories
1.1.1 Test and measurement
1.1.1.1 Testing accessories



Item No.: 210-136
Test plug; 2 mm Ø; with 500 mm cable; red


Installation Notes

Installation



Snapping test plug and spacer modules together to assemble a multipole test plug module.

Testing



Test plugs modules are directly plugged into the jumper contact slot of the current bar.