

Precautions for use

General notes

ML-50-W3BYF

made in JAPAN



Pitch 10.16mm

2-stage

PCB



E101073



Order model number

Order model number ML-50-W3BYF-20P

Order example ML-50-W3BYF-20P

Basic information

Dimension

Soldering heat resistance conditions

Optional

Download

Basic information

Rating	250V-15A
Insulation resistance	DC500V、1000MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL
Position	20
Main insulator	PBT (UL94V-0)
Terminal screw	M4×8 Screw with square washer 、Torque 1.2N・m MAX
Terminal type	PC terminal
Body color	B (Black)
Overview	There is a terminal number display on the body.
Note	1.When tightening the terminal screw without connecting the electric wire, tighten it with a torque of 0.2 to 0.3 Nm.

Home

Product search

Product Category

About SATO PARTS

News classification

Contact us

Video channel

Download brochure

Environmental initiatives

Privacy policy

Download terms

Terms of Use