




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1790329~32	2017/09/19	Lingpeng	Modify The Item No
C	C201071	2020/07/14	Nan_Su	$\triangle$ C X1
D	C210309	2021/03/04	Ruru	$\triangle$ D X4

$\triangle$ D
MSAP-XXPFFP-SF8002


XX: No. Of Pin

Recommended
Panel Cut-Out

6.0 18.4 1.6
3.0
3.0
Connector
Shield
O-Ring
Nut
M16*1.5

22.0 (Hex.)
45°
ALTW
M16*1.5
23.8 (Ref.)

- $\triangle$ D Note:
- * RoHS Compliant
 - * CC Important dimension
 - * Waterproof rate: IPX8, unmated 1m/24h
 - * Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - O-Ring: Rubber, Gray
 - * Shield: Thermoplastic, Black
 - * Nut: Thermoplastic, Black
 - * O-Ring: Rubber, Gray
 - * For panel thickness max: 4.0mm
 - * Nut is packed separately in pe bag



Pin Assignment Front View

UNIT:mm		TITLE N SEN, M12 A -PLASTIC, SCREW RECEPTACLE, F, F, PCB S $\triangle$ D
TOLERANCE	± 0.25 XX ± 0.1 XXX ± 0.05 ANGLES $\pm 1^\circ$	SCALE 3:2 SIZE A4 SHEET 1 OF 2 REV. D WC-REV. .0 CC : Inspection item

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Lingpeng	DATE 2017-09-19
DWG NO MSAP-XXPFFP-SF8002	CHECKED BY Mafei	DATE 2017-09-19
CUSTOMER ALTW	APPROVED BY Jerry	DATE 2017-09-19

安費諾亮泰企業股份有限公司