

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [X-Lok](#) / [Mini Size](#)

Product Line

[Single Pair Ethernet](#) >[ZConnect](#) >[Ceres](#) >[X-Lok](#) >[Accessory](#)[Middle Size](#)[Mini Size](#)[Large Size](#)[Standard Size](#)[M Series](#) >[FLOS & FLOS+](#) >[Power](#) >[RBL](#) >[HS-Lok](#) >[NMEA 2000](#) >[Heavy Duty Shielded](#) >[RJ](#) >[USB](#) >[D-Sub](#) >[HDMI](#) >[DVI](#) >[Fiber Optic](#) >[RF](#) >[Cable Joiner](#) >[Cable Gland](#) >[Pressure Relief Vent](#) >[LED Light Guide](#) >[D-Sub](#) >

AD-04PMMS-QC8001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: UL1977, UL2238

You must login first to view the price

Quantity

- 1 +

Add to Cart

Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Accessory, 5A, 0...
AB-AD-040404-FFM-...
-20°C ~ +85°C

X-Lok, Mini Size, Plasti...
AB-AD04FL-ADFL-...
-20°C ~ +80°C

X-Lok, Mini Size, Plasti...
AB-AD04FL-ADFL-...
-20°C ~ +80°C

X-Lok, Mini Size, Plasti...
AB-AD04FL-ADFL-...
-20°C ~ +80°C

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 5A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 04
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IPX8
Assembly Style Solder	
More Options	

People Also Bought

