


6		5	4	3	2	1
PART NUMBER		TITLE	CABLE DESCRIPTION		LENGTH 'L'	CABLE COLOR
D	2174711101	ULTRA-FIT F-S 75MM 20 AWG LEADS BK Sn	1X20AWG DISC SR-PVC BK UL 1061 HKUP		75±3	BLACK
	2174711102	ULTRA-FIT F-S 150MM 20 AWG LEADS BK Sn	1X20AWG DISC SR-PVC BK UL 1061 HKUP		150±5	BLACK
	2174711103	ULTRA-FIT F-S 225MM 20 AWG LEADS BK Sn	1X20AWG DISC SR-PVC BK UL 1061 HKUP		225±5	BLACK
	2174711104	ULTRA-FIT F-S 300MM 20 AWG LEADS BK Sn	1X20AWG DISC SR-PVC BK UL 1061 HKUP		300±5	BLACK
	2174711105	ULTRA-FIT F-S 450MM 20 AWG LEADS BK Sn	1X20AWG DISC SR-PVC BK UL 1061 HKUP		450±5	BLACK
	2174712101	ULTRA-FIT F-S 75MM 20 AWG LEADS RD Sn	1X20AWG DISC SR-PVC RD UL 1061 HKUP		75±3	RED
	2174712102	ULTRA-FIT F-S 150MM 20 AWG LEADS RD Sn	1X20AWG DISC SR-PVC RD UL 1061 HKUP		150±5	RED
	2174712103	ULTRA-FIT F-S 225MM 20 AWG LEADS RD Sn	1X20AWG DISC SR-PVC RD UL 1061 HKUP		225±5	RED
	2174712104	ULTRA-FIT F-S 300MM 20 AWG LEADS RD Sn	1X20AWG DISC SR-PVC RD UL 1061 HKUP		300±5	RED
	2174712105	ULTRA-FIT F-S 450MM 20 AWG LEADS RD Sn	1X20AWG DISC SR-PVC RD UL 1061 HKUP		450±5	RED



ITEM	PART#	DESCRIPTION	QTY	UOM
A	1722537123	ULTRA-FIT CRIMP TERM 20-22 TIN Pre-P	1	PC

- NOTES:
1. CRIMPING TO BE DONE AS PER MOLEX STANDARDS.
 2. THE PRODUCT SPECIFICATION RELIES ON THE TERMINALS & WIRE SPEC.
 3. FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1MM. TINNING DIA MUST BE 1.25MM MAX.

REVISION				
DATE	REV	DESCRIPTION	CHANGER	
2021/02/05	A	INITIAL RELEASE	ARAJU	
DOCUMENT STATUS	P1	RELEASE DATE	2021/02/05	09:09:22

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
FUNCTIONAL SYMBOLS F = 0 F = 0 F = 0 DIVISIONAL SYMBOLS		DIMENSION UNITS		SCALE		CURRENT REV DESC: EC NO: 654817 DRWN: ARAJU 2020/12/03 CHK'D: RDESAI01 2021/02/05 APPR: RDESAI01 2021/02/05 INITIAL REVISION: DRWN: ARAJU 2020/12/03 APPR: RDESAI01 2021/02/05					molex					
		mm		NTS												
		GENERAL TOLERANCES (UNLESS SPECIFIED)									SEE TABLE					
		ANGULAR TOL ± °														
DIVISIONAL SYMBOLS		4 PLACES		±		PRODUCT CUSTOMER DRAWING										
		3 PLACES		±												
		2 PLACES		±		DOCUMENT NUMBER			DOC TYPE		DOC PART		REVISION			
		1 PLACE		±		2174711101			PSD		000		A			
		0 PLACES		±												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER		
						A4-SIZE		217471		SEE TABLE		GENERAL MARKET		1 OF 1		

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

2174711101

DOC TYPE

PSD

DOC PART

000

REVISION

A