

Industrial Rated Plug & Play Ethernet Switches

Weidmüller's Basic Line consists of unmanaged switches in a rugged IP30 rated aluminium housing.

- Compact design
- Built in Broadcast Storm Protection via DIP switches
- No programming required
- Fast Ethernet variants with 5- and 8-Ports 10/100BaseT(X) (RJ45 connector)
- Operating Temperature: -10°C to +60°C
- Approvals: cULus, Class I Div. 2 / ATEX, DNV / GL



Special Price from \$105.50



Catalog #	Description	Regular Price	Special Price
1240840000	IE-SW-BL05-5TX	\$150.10 ea.	\$105.50 ea.
1240900000	IE-SW-BL08-8TX	\$218.00 ea.	\$153.90 ea.

QUOTATION #Q4-2013

This number must appear on purchase order to receive special prices.

Valid from October 1st until December 31st, 2013

Q-Specials 2013

4th Quarter

Special Price from \$16.00



connectPower[®] Branch Rated Circuit Breakers

We have now expanded our product offering of UL489/CSA C22.2 No.5-02 and UL1077/CSA C22.2 No.235 compliant 1, 2 and 3-pole-type circuit breakers from 0.5 to 60 Amperes and with type C and D characteristics.

- 277/480V rated (<30A)
- 240V rated (<63A)
- cULus approval
- Screw or ring-lug termination options
- High vibration / mechanical shock resistance



A selected few are on special this quarter.

Catalog #	Description	Regular Price	Special Price
BR1C1AC	Branch/1P CctBrkr/C Curve/1A	\$21.40 ea.	\$16.00 ea.
BR1C2AC	Branch/1P CctBrkr/C Curve/2A	\$21.40 ea.	\$16.00 ea.
BR1C5AC	Branch/1P CctBrkr/C Curve/5A	\$21.40 ea.	\$16.00 ea.
BR1C10AC	Branch/1P CctBrkr/C Curve/10A	\$21.40 ea.	\$16.00 ea.
BR1C15AC	Branch/1P CctBrkr/C Curve/15A	\$21.40 ea.	\$16.00 ea.
BR1C20AC	Branch/1P Cct Brkr/C Curve/20A	\$21.40 ea.	\$16.00 ea.
BR1C25AC	Branch/1P CctBrkr/C Curve/25A	\$21.40 ea.	\$16.00 ea.
BR1C30AC	Branch/1P CctBrkr/C Curve/30A	\$21.40 ea.	\$16.00 ea.
BR1C40AC	Branch/1P CctBrkr/C Curve/40A	\$23.50 ea.	\$17.50 ea.
BR1C50AC	Branch/1P CctBrkr/C Curve/50A	\$23.50 ea.	\$17.50 ea.

Weidmüller Canada Infoline : 1-800-268-4080
Weidmüller Canada Fax : 1-877-300-5635
support@weidmuller.ca ISO 9001:2008 Registered
For an electronic copy of this Q-Special :
http://www.weidmuller.ca/q-specials_ca



Q-Specials

Special Price from \$150.00



ACT20M - Analogue Signal Isolators in a 6mm Wide Housing

NEW - Bipolar input versions - 3/4 way isolated

- 1375450000: Isolating and converting of Bipolar DC voltage or current signals, single unipolar output
- 1375470000: Isolating and converting of Bipolar DC voltage or current signals, dual unipolar output (splitter function)

Output Loop Powered Isolators - 2 way isolated

- 1176040000: Single channel 4-20mA loop Isolator with active input and passive output
- 1176050000: Dual channel 4-20mA loop Isolator with active input and passive output

Universal converters - 3 way isolated

- 1176030000: Isolating and converting of temperature signals and DC signals
- 1176000000: Isolating and converting DC voltage or current signals

Signal splitters - 4 way isolated

- 1175990000: Isolating, converting and splitting current loop signals
- 1176020000: Isolating, converting and splitting DC voltage or current signals

Passive Input Loop Powered Isolators for 4-20mA current loops - 2 way isolated

- 1176070000: Single channel, input loop powered with passive input and active output
- 1176080000: Dual channel, input loop powered with passive input and active output

DC Isolator - 3 way isolated

- 1175980000: Isolating of 4-20mA current loop signals

Common Features

- Ambient temperature (operational): -25°C...+70°C
- Optionally supplied via the Power Rail-bus (3 or 4 way isolated units only)
- High level of galvanic isolation up to 2.5kV
- cULus 61010-1, cFmus Div. 2, ATEX Zone 2, DNV, GL

Catalog #	Description	Regular Price	Special Price
1375450000	ACT20M-BAI-A0-S	\$240.90 ea.	\$180.00 ea.
1375470000	ACT20M-BAI-2A0-S	\$326.90 ea.	\$245.00 ea.
1176040000	ACT20M-CI-C0-OLP-S	\$217.40 ea.	\$165.00 ea.
1176050000	ACT20M-2CI-2C0-OLP-S	\$326.90 ea.	\$250.00 ea.
1175980000	ACT20M-CI-C0-S	\$201.80 ea.	\$150.00 ea.
1175990000	ACT20M-CI-2C0-S	\$295.60 ea.	\$220.00 ea.
1176000000	ACT20M-AI-A0-S	\$287.80 ea.	\$215.00 ea.
1176020000	ACT20M-AI-2A0-S	\$326.90 ea.	\$240.00 ea.
1176030000	ACT20M-UI-A0-S	\$326.90 ea.	\$240.00 ea.
1176070000	ACT20M-CI-C0-ILP-S	\$217.40 ea.	\$160.00 ea.
1176080000	ACT20M-2CI-2C0-ILP-S	\$326.90 ea.	\$240.00 ea.

Special Price \$200.00



Stripax® Plus Crimp Set

The Stripax® Plus cuts, strips and crimps reel-packaged wire end ferrules onto individual wires 0.5...2.5 mm² - all with a single tool.

- PSC 01 assortment box, clear with foam insert
- Stripax® Plus combination tool for processing strips of linked wire-end ferrules of 0.5...2.5 mm² from Weidmüller
- Wire-end ferrules with plastic collars H 0.5...H 2.5
- Weidmüller colour code

Catalog #	Description	Regular Price	Special Price
9028770000	CRIMP-SET STRIPAX PLUS	\$316.40 ea.	\$200.00 ea.

Special Price \$5.20



Swivel Head Screwdriver

- Slotted screwdriver with swivel head for ease of use
- The shaft is 60mm in length
- The blade is 3.5mm wide and 0.6mm in thickness
- Ideal for 2.5 and 4mm² screw clamp terminals

Catalog #	Description	Regular Price	Special Price
9918110000	SD 0,6x3,5x60 pico SWIVEL HEAD	\$10.90 ea.	\$5.20 ea.

Special Price \$8.90



Angled Slotted Screwdriver

This special angled tip screwdriver is specifically designed to be used with our screwless terminals of the Z and P Series. Compared to its straight counterpart, it provides a clearer view of the wire entry port for these blocks where the wire and clamp opening holes are on the same plane. Its 3.0mm wide tip is ideal for opening tension clamp and Push-In terminals as small as 2.5mm²

Catalog #	Description	Regular Price	Special Price
1323880000	SD TO 0.6X3.0	\$12.70 ea.	\$8.90 ea.

HELP US CONSERVE!!!

If you would prefer an electronic copy, contact: marketing@weidmuller.ca

CONDITIONS : Prices valid from October 1st, 2013 to December 31st, 2013. Orders must be received by Weidmüller by this date. Orders must be sent to an authorized Weidmüller distributor. Orders must reference quotation number Q4-2013. Please note that all prices (Regular Price and Special Price) are suggested pricing only.

Cut a Perfect Rectangular Hole Every Time!

Hydraulic Hole Puncher

The IP protection classes for housings, cable glands, heavy-duty connectors and Industrial Ethernet connectors can only be maintained under two conditions: the sheet metal must not be bent during the punching process and the size of the punched-out holes must correspond precisely with the specifications. The IE-KO-HAT hydraulic sheet metal hole puncher, together with its accessories, guarantees you the highest quality workmanship available. It ensures that the connector fits precisely with the punched-out holes so that you can fulfill the proper IP protection class requirements.



Technical Features

- Overpressure valve protects against overloading
- Cylinder head angled 90°
- Angled head can be rotated through 360°
- Ergonomic handle springs back automatically
- The piece of waste no longer becomes jammed thanks to 3-fold cleaving
- Hydraulic punch manufactured from high-strength aluminium (approx. 40% less weight)

Available Die Set Stamps

Die sets or Stamps are available in the following formats:

- 4 special sizes for Industrial Ethernet Connectors
- 4 rectangular splitting stamps for heavy-duty connectors in size 3, 4, 6 and 8
- 2 square splitting stamps for switches
- 5 metric round stamps from M16 to M40
- 7 PG round stamps from PG 9 to PG36

Type IE-KO-HAT

Catalog # 1966810000

Included accessories:

- 1 hydraulic screw Ø 19 mm
- 1 hydraulic screw Ø 19 x 9.5 mm
- 1 HSS pre-drill Ø 10 mm
- 1 spacer nut set (3-part)
- 1 bridge
- Die sets sold separately



The hydraulic hole puncher punches out precise holes for accommodating metric and PG cable glands.



Automatic centre punching at the drill points when punching out holes for heavy-duty connectors.



Punching out holes for a variety of industrial Ethernet connectors.



Round splitting stamp for high-strength cable glands



Rectangular splitting stamp for heavy-duty connectors



Custom stamp for industrial Ethernet connections



Rectangular splitting stamp for switches



Tension screw

Visit our Q Special website for complete ordering information of our stamp die sets and accessories for the IE-KO-HAT tool.

http://www.weidmuller.com/90734/News/Q-Specials/Canada/cw_index_v2.aspx

Weidmüller 

THM Plus S Printer and TwinMark Endless Heat-Shrinkable Sleeves

NEW


Individual, Accurate Wire Identification

Being able to identify individual wires in the cabinet significantly minimizes errors and their elimination. The THM Plus S Printer and TwinMark endless heat-shrinkable sleeve system enables fast, reliable results, which reduces costs from the word go.

How can data from a design system be applied onto the wire in space-saving form? Without having to invest a lot of effort or time? Whilst ensuring that the data is clearly legible and remains so for a long time?

The TwinMark endless heat-shrinkable sleeve is printed in a matter of seconds using thermal transfer printing. Depending on the number of characters or the available space, the length of the marker can be individually adjusted and shrunk to the correct size, onto the wire.

After importing the data with our M-Print® PRO software and printing with the THM Plus S printer, the shrinkable sleeve is perforated to the desired length and is immediately ready to use.



Saving Space On the Wire

The individual marker is pushed onto the wire and is firmly seated even without shrinking. However, a really tight fit can be achieved with a shrink rate of 2:1.

THM Plus S Printer

The THM Plus S thermal transfer printer is the ideal solution for labels or shrink sleeves. A touch display and the centrally guided roller facilitate handling.

Wide Range of Diameters

The portfolio covers a diameter range from 1.2 mm to 25.4 mm. The standard colours are white and yellow. Special colours are available on request.

Easy Opening

To save installation time, pressing gently on the side is sufficient to open the sleeve. This is ensured by its slight oval shape.



Perforation To the Desired Length

The marker is set to the desired length using the software. A perforation cutter ensures ease of separation. The sleeve, as a whole, remains intact.

High-Quality Material

The halogen-free polyolefin has been tested according to DIN 5510-2 and BS 6853. It is therefore suitable for applications in the traffic engineering, marine or offshore sectors.

Ink Ribbon

To guarantee optimum resistance, we offer an ink ribbon developed specifically for this purpose.



Perforation Cutter

This module is available as an option for the THM Plus S printer and corresponds with the TwinMark endless shrink sleeve. Simple to install in a matter of seconds.



Ordering Data

Type	Catalog #
THM PLUS S Printer	1327170000
Accessories	Catalog #
M-PRINT PRO software	1905490000
THM PLUS S PERFV Perforation Cutter	1416330000
THM PLUS S SCHV Cutting Blade	1331600000
RIBBON HSS HF EL 40/300 Ribbon (40mm wide)	1426210000

Visit our Q Special website for complete ordering information of our endless heat-shrinkable sleeves available in white and in yellow.

http://www.weidmuller.com/90734/News/Q-Specials/Canada/cw_index_v2.aspx

Weidmüller 