

MATERIAL AND FINISH:

Insulator: Polycarbonate, UL-94V-0 rated
Contacts: Brass

ELECTRICAL SPECIFICATIONS:

Current rating: 10 A/15 A
Voltage rating: 250 VAC
Insulation resistance: 100 Mohm min. at 500 VDC
Dielectric withstanding voltage: 2000 VAC for one minute

ORDERING CODE:


43R05-1 3 1 2

1) COLOR



- 1 = BLACK
- 2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION

- 1 = 10A 250V 70°C   
- 2 = 10A 250V 120°C   
- 3 = 10A 250V 155°C  



RECOMMENDED
PANEL CUTOUT



RoHS
COMPLIANT

REVISIONS

REV	DATE	CHANGE	CHNG	CHK	APPR
A	11/21/05	ADD RoHS	PB		

TOLERANCE
UNLESS OTHERWISE SPECIFIED
X ± 1
X.X ± 0.4
X.XX ± 0.20

DRAWN BY	GQ	DATE:	10/08/01
CHECK BY	TD	DATE:	10/18/01
APPR BY	PB	DATE:	10/18/01

Power Dynamics, Inc.
Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076
PART: 10A/15A IEC 60320 APPL. OUTLET; QC
TERMINALS: SIDE FLANGE, PANEL MOUNT

PART #:	43R05-1X3X	SHEET	1 of 1
SIZE:	A	ALL DIMENSIONS FOR REFERENCE ONLY	REV: A
SCALE:	NTS	DIMENSIONS ARE IN MILLIMETERS	