

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)[Home](#) / [Products](#) / [USB](#) / [Type B 2.0](#)


Product Line

- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >

- Type C 3.2 Gen1
- Type C 3.2 Gen2
- Type A 3.2 Gen1
- Mini B 2.0
- Micro AB 2.0
- Micro B 2.0

- Type A 2.0
- Type B 2.0
- Type C 2.0
- Accessory

- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



UB-20BMFA-SL8001

- Operating Temperature: -20°C ~ +80°C
- Transmission Speed: USB 2.0
- Shielded: Plastic, Shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Check Stock

- Add to Cart
- Inquiry
-



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

▼

Search

ABOUT AMPHENOL LTW

SUPPORT

PARTNERS

DOWNLOAD CENTER

FEEDBACK

- 0 +

- 0 +

- 0 +

- 0 +

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 1.5A	Connector Type Field Installable
Shielded Plastic, Shielded	No. of Contacts N/A
Connector Gender Male	Backshell Straight
Mating Style Screw Thread	IP Rating IPX8
Assembly Style Solder	
More Options	

People Also Bought

