

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PROSPER, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RW82T

BZ-2RW82T
PAGE 1 OF 1

M
DRAWING
NUMBER

7

ISSUE

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO 16736 GCH 13 APRIL 62
B	CO- 69351-D JWB 18 JUL 91
C	CO- 752048 KDR 1 FEB 94
D	CO- 77589 MAN 29 MAR 94
E	CO93346 DLT 11 SEP 98

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE

△ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA		SCALE FULL
OPERATING FORCE----- 3 1/2 OZ MAX	CONTACT ARRANGEMENT S P D T	BREAK DISTANCE .020 MIN	DO NOT SCALE PRINT
RELEASE FORCE----- 3/4 OZ MIN	UNDERWRITERS' LAB. INC. LISTED RATING		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL----- .004-.040	-L96- 15A-125, 250, OR 480 VAC		TOLERANCES ARE:
OVERTRAVEL----- .156 MIN	1/2 A-125 VDC; 1/4 A-250 VDC		ONE PLACE (.0) ±.030
	1/8 HP-125 VAC; 1/4 HP-250 VAC		TWO PLACE (.00) ±.015
	-L288- CE D SP		THREE PLACE (.000) ±.008
	-L299- 16A 250V ~ T85 5E4		ANGLES ±
	-L306-		WEIGHT .076 LB

FORMTEK

FO-90378

DRAWN

GCH 13 APRIL 62

4 MAY 62

REVISIONS

CHECK

ISSUE

RELEASE NO.

REPLACES