

Precautions for use

General notes

F-400-01A2

made In JAPAN



Bayonet Cap

Electric shock safety

2020-01-09

Notice of partial product changes. PDF

See other change notifications

UL

E101405

Download

Warning

40012892

Download

Order model number

Order model numberF-400-01A2

Order exampleF-400-01A2

- Basic information
- Dimension
- Soldering heat resistance conditions
- Conformity product / Mate product
- Download

Mating fuse size

5.2mm×20mm

Basic information

Rating	250V-10A
Insulation resistance	DC500V, 100MΩ Min
Withstand voltage	AC2000V (1minute)
Certificates & Approvals	UL・CSA(C-UL)・VDE
Main insulator	Phenolic (UL94V-0)
Cap insulator	PBT (UL94V-0)
Terminal type	Both soldering and 0.187in. tab terminal (t0.5mm(0.020in.)) for quick-connect terminations.
Body color	B (Black)
Cap color	B (Black)
Panel thickness	7.5mm Max
Nut torque	0.8N・m
Applicable tool for cap	Screw driver

List of partial product change notifications

2020-01-09	Notice of partial product changes. PDF
2019-08-01	Notice of partial product changes. PDF
2017-09-06	Notice of partial product changes. PDF
2011-04-04	Notice of partial product changes. PDF
2009-12-15	Notice of partial product changes. PDF

Related products

F-75



F-75

Add to My List