

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BE-R24-A4**BE-R24-A4****M**DRAWING
NUMBER

ISSUE	8
3	8

REPLACES

SR 11992

RELEASE NO.


CHECK

REVISIONS

A	SR11992	6 OCT 65
B	CO36627	5 APR 76
C	CO 58782	24 JAN 86
D	CO 73287-G	20 OCT 93
E	CO 77591	22 JUN 94
F	CO 79599E	24 FEB 95

DRAWN

C-30378

**NOTE -**

1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF $.139 \text{ MAX DIA}$ ON $1.000 \pm .002$ CENTERS
2- SWITCH WILL WITHSTAND TEMPERATURE OF 275°F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 11-17 OZ
RELEASE FORCE — — — — — 10 OZ MIN
DIFFERENTIAL TRAVEL — — .0015-.0025
OVERTRAVEL — — — — — .010 MIN

ELECTRICAL DATA**CONTACT ARRANGEMENT**
S P D T

25A-125, 250 OR 480 VAC
3/4 HP-125 VAC: 1 1/2 HP-250 VAC
PILOT DUTY: 375 VA-125, OR 250 VAC
60/75°C (Cu)

**SCALE FULL****DO NOT SCALE PRINT****UNLESS OTHERWISE NOTED****DIMENSIONS ARE IN INCHES****TOLERANCES ARE:**

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .005$
ANGLES		$\pm$

WEIGHT .063 LB