




HOME



会社概要

環境に対する  
取り組みカタログ・サンプル  
STEPファイル請求

問い合わせ

We contribute to manufacturing with delivery time, quality, and service.

[Employment Information](#)[Site Map](#)E-Mail: [marketing@satoparts.co.jp](mailto:marketing@satoparts.co.jp)

## Model number search

 
Model number search  
within category
 

## [Refine search]


By application / shape

By classification

- ☐ Terminal
- ☐ Chip jack

## Supplementary information (PDF)

- ▶ Handling precautions
- ▶ General notes

スクルーレス端子台  
Screwless Terminalネジ式端子台  
Screw Terminalヒューズホルダー、  
ヒューズ管  
Fuse Holder, Fuse表示台、LEDブラケット、  
ネオンブラケット  
Indicatorツマミ  
Knobコンセント、コネクタ  
Connectorターミナル、チップジャック  
Terminal, Tip Jackクリップ、ソケット、プラグ  
Clip, Socket, Plugブッシング、ラグ板  
Bushing, Lugアクセサリ  
Accessory[home](#) > [List of terminals and chip jacks](#) > TJ-1

## TJ-1



made in Japan

[Information on the RoHS Directive](#)

## Body color



## specification


|                        |                                                                 |
|------------------------|-----------------------------------------------------------------|
| Rated                  | 30V-5A                                                          |
| Withstand voltage      | AC1000V (1 minute)                                              |
| Insulation resistance  | DC500V, 100MΩ or more                                           |
| Panel mounting method  | Nut tightening                                                  |
| Nut tightening torque  | 0.1 N · m or less                                               |
| Nut width across flats | 8.0mm                                                           |
| Main insulation        | Nylon 6                                                         |
| Body color             | B (black), R (red), BL (blue), Y (yellow), G (green), W (white) |
| Conformity product     | <a href="#">TJ-2-P</a>                                          |

## Dimensional drawing



[Product Summary](#) / [Color](#) / [specification](#) / [Dimensional drawing](#) / [Order model number](#) / [Solder heat resistance conditions](#) / [download](#)

Request STEP files and samples of the product you are currently



Unit: mm

Order model number

Order model number TJ-1- [body color]  
Order example TJ-1-R (when ordering in red)

Solder heat resistance conditions

Hand soldering (soldering ironing) conditions

|                      |           |
|----------------------|-----------|
| Iron tip temperature | 360 °C    |
| Iron guessing time   | 3 seconds |
| Number of times      | Twice     |

Notes

- Flow / Reflow is not applicable.
- Perform the second soldering with a soldering iron after the product has cooled sufficiently and returned to room temperature after the first soldering.
- When using it, we recommend that you check it according to the actual usage conditions. The above conditions have been confirmed by testing the product itself.

DXF / Environmental Hazardous Substances Report (chemSHERPA) Download

\* Please read the [DXF file terms of use](#) when downloading the [DXF file](#) .  
\* For the Environmentally Friendly Substances Report , please see our [Environmental Initiatives](#) .  
\* For tools for viewing chemSHERPA data, see the [PDF download procedure manual](#) .

|         |          |
|---------|----------|
| TJ-1    | download |
| TJ-1-B  | download |
| TJ-1-BL | download |
| TJ-1-G  | download |
| TJ-1-R  | download |
| TJ-1-W  | download |
| TJ-1-Y  | download |