

SATO PARTS CO.,LTD. > Product Category > Screwless Terminal Blocks


Product mass

Precautions for use

General notes

ML-860-VBX

made in JAPAN



Pitch 10mm

for power supply

Solid wire only

2025-12-19PDF

See other change notifications

Order model number	
Order model number	ML-860-VBX
Order example	ML-860-VBX

Basic information

Dimension

Soldering heat resistance conditions

Download

Basic information

Rating	250V 20A
Insulation resistance	100MΩ (1 minute)
Withstand voltage	AC2000V (1minute)
Position	3
Main insulator	PBT (UL94V-0)
Button insulator	PBT (UL94V-0)
Rating wire	Φ2.0mm
Wire range	Φ1.2mm～Φ2.0mm
Terminal type	PC terminal
Wire strip length	14mm
Body color	GY (Gray)
Button color	B (Black)
Applicable tool for button	Screw driver or others
Installation	Screw
PCB thickness	1.6mm
Note	1.Fluororesin is applied to the buttons to facilitate the operation of the buttons. It may appear that white foreign matter has adhered due to the concentration and retention of this fluororesin in the concave parts of the button operation part, but there is no problem with the quality.
Caution	1.Don't immerse and wash this product in liquid.

List of partial product change notifications

2025-12-19PDF