






Copyright FCI.

D




LAYOUT DIMENSIONS (after plating)
CONNECTOR SIDE VIEW




REV F - 2006-04-17

2



3

DETAIL OF PRESS FIT
Scale: 3



DE02V2P93C6G40	UNC 4.40
DE02V2P93C5G40	UNC 4.40
DEL2V2P93C6G40	M3
DEL2V2P93C5G40	M3
PART NUMBER	Threaded A

GENERAL CHARACTERISTICS : SEE DRAWING C01-8639-0002

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	1997/05/06	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	1997/05/06			0.XX	±0.1				
Chr	LEGARE	1997/05/06			0.XX* ±2*	±0.1				
Appr	LEGARE	1997/05/06	Product family		D-SUB		ECN		LS06-0097	
							Spec ref -			
			title MALE CONNECTOR 2V2 with s power press fit			dwg no C01-8639-1525			Rev. J	
			catalog no -			CUSTOMER			sheet 1 of 1	

rev	ecn no	dr	date
F	-	BAR	2003/11/07
G	LS05-004	MPE	2005/02/08
H	LS05-0090	LGO	2005/10/13
J	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

PDM: Rev J

STATUS: Released

Printed: May 25, 2022