


LK425-A/X



Item number 28.0119- *

Highly flexible, with stackable Ø 4 mm MULTILAM plugs on both ends.

Technical data	
Diameter of plug system	4 mm
Rated Values	30 VAC, 32 A / 60 VDC, 32 A
Surface treatment electrical contact	Ni
Base material electrical contact	CuZn
Lead cross section	2.5 mm²
Lead lengths	25 cm; 50 cm; 75 cm; 100 cm; 150 cm; 200 cm
Lead insulation	PVC
Colours *	20 21 22 23 24 25 26 27 29
Test accessory acc. to	IEC EN 61010-031