






THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	2/8/12	D. GRIFFIN
B	ECN9776: CORRECTED JACK ORIENTATION	02/15/12	DJP
C	ECN 7494: CLARIFIED WIRE MAP, UPD ROHS, FORMAT, DWG LAYOUT	7/25/14	D. DESJARDIN



NOTES:

- MATERIAL:**
SERIES "A" JACK:
PANEL MOUNT HOUSING: PVC
CONNECTOR PLASTIC: (BLUE) PBT WITH GLASS FIBER
CONNECTOR CONTACTS: BRASS
CONNECTOR SHELL: SUS
- SERIES "A" PLUG:**
CONNECTOR SHELL: SPCC
CONNECTOR PLASTIC: (BLUE) PBT WITH GLASS FIBER, UL94V-0
CONNECTOR CONTACTS: PHOSPHOR BRONZE
- FINISH:**
CONNECTOR CONTACTS: GOLD, 30µINCHES
CONNECTOR SHELL: NICKEL
- ENVIRONMENTAL:**
OPERATING TEMPERATURE: -20°C TO +80°C
- MISCELLANEOUS:**
CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031
- REGULATORY COMPLIANCE:**
CE2011/65/EU (RoHS Directive)



PART NUMBER	LENGTH METERS [FEET]
UPMAA-30-03M	0.3 [0.98]
UPMAA-30-05M	0.5 [1.64]
UPMAA-30-1M	1.0 [3.28]
UPMAA-30-2M	2.0 [6.56]
UPMAA-30-3M	3.0 [9.84]

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (mm) OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS		DATE	L-com® Global Connectivity 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY D. PARHAM		09/22/2011	
	CHECKED BY D. CASTRO		09/22/2011	
	APPROVED BY S. SMITH		09/27/2011	
	CATEGORY USB			
PRODUCT DESCRIPTION CA USB 3.0 A PNL/AM				
ALL OTHER DIMENSIONAL TOLERANCES: XX = ±.02 [51] XX = ±.01 [25] XXX = ±.005 [127]	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY			
	SIZE A	FSCM NO. 43321	DWG. NO.	REV. C
	COLOR VARIATIONS MAY OCCUR			
	SCALE: NONE	CAD FILE: UPMAA-30.SLDDRW	SHEET 1 OF 1	
	PROJECTION 			