

[Products](#)[Customize Your Parts](#)[Industries Solutions](#)[Search](#)[News & Events](#)[First Time?](#)

(0)



Home / Products / X-Lok / Mini Size

Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

X-Lok >

- Accessory
- Middle Size
- Mini Size
- Large Size
- Standard Size

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 2000 >

Heavy Duty Shielded >

RJ >

USB >

RF >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



AG-05PMJS-QC800P

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A


You must login first for view the price

Quantity - 1 +

Check Stock

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search

X-Lok, Mini Size, Plasti...
AG-05BFGM-QL8G01
-20°C ~ +85°C

X-Lok, Mini Size, Plasti...
AG-05BFGM-QL8G02
-20°C ~ +85°C

X-Lok, Mini Size, Plasti...
AG-05BFGM-QL8G03
-20°C ~ +85°C

X-Lok, Mini Size, Plasti...
AG-05BFGM-QL8G04
-20°C ~ +85°C

Add to Cart

Inquiry

Specifications	Download / CAD
Nominal Current 16A	Connector Type Receptacle
Shielded Plastic, Non-shielded	No. of Contacts 05
Connector Gender Male	Backshell Circular
Mating Style Push Lock	IP Rating IPX8
Assembly Style Solder	
More Options	

People Also Bought

