




NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
2. BRASS PER QQ-B-613
3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
4. PHOSPHOR BRONZE PER QQ-B-750
5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE

1. MAX. PANEL THICKNESS=5.5mm

						DIMENSIONS ARE IN MILLIMETERS				PART NO. B7771B3-ND3G-75		Amphenol TITLE BNC FEMALE TO FEMALE BULKHEAD ISOLATED ADAPTOR DRAWING NO. KJ-B7771B3-ND3G-75 ITEM NO.		
7	HEX NUT	NOTE 1	NOTE 3	1	HN16-1/2-28X28	UNLESS OTHERWISE SPECIFIED TOLERANCES 0.5-6 = ±0.2 6-30 = ±0.4 30-120 = ±0.6 120-315 = ±1 315-1000 = ±1.6 1000-2000 = ±2.4				APPROVED			DATE 10-11-01'	
6	LOCK WASHER	NOTE 2	NOTE 3	1	LW-16/13X05					CHECKED			DATE 10-11-01'	
5	LOCK RING	NOTE 2	NOTE 3	1	B7700-4					DRAWN			DATE 10-11-01'	
4	CONTACT PIN	NOTE 4	NOTE 5	1	B7900-4									
3	INSULATOR	DELTRIN	NATURAL	2	B7996ZZ-3-75									
2	INSULATOR	DELTRIN	WHITE	1	B7771B3-1P									
1	BODY	NOTE 1	NOTE 3	1										
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	A	FILE NO.				