

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED AS PER ECN-25-351332	28OCT2025	PSK	J.M

Ø1.75 MIN

Suggested PCB Footprint

2-C0.05

0.8


Ø1.5

Note: Remove all sharp edges, burrs & pip

ENVIRONMENTAL PARAMETER	
TEMPERATURE RANGE	-55 ~+125 °



MATERIALS AND PLATING UNIT: MICRO-INCHES	
MATERIALS	PLATING
BRASS ALLOY	GOLD10u"/NICKEL 50u"

2511420-1 - AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP SK CHK MADHAN S APVD JAGRUTI M	20JUN2025 20JUN2025 20JUN2025	 TE Connectivity Ltd.					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME					
		0 PLC ± -		CONTACT PAD 1.50Dx0.80H GOLD					
		1 PLC ± 0.2		-					
		2 PLC ± 0.1		-					
		3 PLC ± 0.05		-					
		4 PLC ± -		-					
MATERIAL		FINISH		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE		SEE TABLE		WEIGHT 0		A2	00779	C-2511420	-
CUSTOMER DRAWING						SCALE	1:1	SHEET 1 of 2	REV A1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

NOTES :
1.PRIMARY PACKING: 2500 PCS/DISH(2500PCS)
2.OUTER PACKING: 4 DISH/CARTON(10000PCS)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRATHAP SK 20JUN2025	 TE Connectivity Ltd.			
		CHK MADHAN S 20JUN2025				
DIMENSIONS: mm [INCHES]		APVD JAGRUTI M 20JUN2025	NAME CONTACT PAD 1.50Dx0.80H GOLD			
		PRODUCT SPEC 108-162165				
		APPLICATION SPEC	RESTRICTED TO			
MATERIAL -		FINISH -				
		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 of 2	REV A1