



Emergency Stop FF01 Series FF01-16BAREYG3



*The photo is a sample image.
 The actual color and shape may differ.
 *Please be sure to check the actual color and shape with a product sample.

3D CAD

PDF

Product Introduction	
Compact Emergency Stop Push Button Switch (FF01 Series) - Solder Terminal Type - Single Pole Single Throw - No Arrow Indicator - Φ25 - Function: Lock Type (Push Lock, Pull or Turn Reset) - Panel Seal Mechanism - IP65 - UL/TUV Certified - Operating Temperature Range: -25 to 60° C - Applications: Small Wireless Control Panels, Teaching Pendants, Portable Devices, Handheld Devices - EU-RoHS Compliant - Model Number: FF01-16BAREYG3	
Product overview	
Model Name	FF01-16BAREYG3
category	emergency stop
series	FF01
Subcategory	Non-illuminated switch
Current capacity for detailed display1	0.5A DC24V
Operating temperature range (° C)	-25/+60
Number of poles	Unipolar
Function 1	ON-OFF
Function 2	rock
Operation part shape	Circle 25
Terminal shape	Solder terminals
Environmental performance	RoHS

Functionality-enhancing accessories
▶ Jig AT-119
▶ Switchguard AT-220 (Switchguard - Yellow)
▶ Nameplate AT-221 (Nameplate - Yellow)
▶ Nameplate AT-222 (Nameplate - Yellow)
▶ Nameplate AT-223 (Nameplate - Yellow)
▶ Nameplate AT-224 (Nameplate - Yellow)

Total 6 items

Back to Series TOP