


No.	Changes and/or Note No.	Date	Intr.	No.	Changes and/or Note No.	Date	Intr.



UNIT: (mm)

DIMENSIONS

Size:	A	B	C	D	E	Part No:
09P	30.81	24.99	11.08	16.92	8.31	MH10567
15P	39.14	33.32	19.39	25.25	16.62	MH10568
25P	53.04	47.04	33.24	38.96	30.47	MH10569
37P	69.36	63.50	49.86	55.25	47.09	MH10570

Material Specification:

Shell: Steel, Tin Plated (Standard)
 Insulator: Glass Filled PBT, UL 94 V-0
 Contacts: Copper Alloy
 Plating: 1.5µ Tin and 0.2µ Gold

Electrical Specification:

Current Rating: 1.5 Amp
 Contact Resistance: less than 10 mΩ
 Test Voltage: 1000V
 Operating Temperature: -55°C to +125°C

DATE	DRAWN MRR	SCALE	MATERIAL TYPE	
	APPROVED		REPLACES	
	105 - Series Sub-D IDC Male UNC 4-40 Clinch Nuts			 DRAWING No