

MHDTPK SERIES

Category: Choose Category

FEATURES

- Available in sizes 9, 15, 25 and 37-way
- Suitable for any common D-Sub connector
- Strain relief inserts ensure a secure termination
- Easy to reopen
- Also available as an unshielded (MHDTPPK) or metal (MHDTZK) version



SPECIFICATIONS

Housing Material:	ABS, UL94 HB
Housing Plating:	Nickel over Copper
Operating Temperature Range:	-55°C to +110°C
Cable Entry:	Top
Thumbscrews:	UNC 4-40 (Standard), M2.5 or M3 (On Request)
Cable Outer Diameter:	Up to 13mm

VIDEO:



Check Inventory



Resource Center



Compliance



Custom Connectors

STANDARD D-SUB HOOD | TOP ENTRY

FILTER ↓

Search Part Number

OR

MHDTPK9-DB9S-K

SEARCH

	PART #	POSITION	HOUSING MATERIAL	DRAWING	ORDER SAMPLES
	MHDTPK9-DB9S-K	9	N/A	N/A	

RELATED SERIES



STOCKING DISTRIBUTORS

COOKIE POLICY

This site uses cookies and other tracking technologies to assist with navigation and your ability to provide feedback, analyse your use of our products and services. [Cookie Policy](#).

I ACCEPT

Resource Center
About Us
Contact Us

NEWSLETTER SIGN UP

Enter Email Address

