


REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A3	—	RELEASE NEW DWG FORMAT	03SEP13	JARRY	
A4	—	ADDED COLOR CHART& GREEN COLOR	23SEP14	JAH	
A5	—	INCREASE THE SPECIAL-SHAPED HOLE FOR AHDC-09T	02NOV20	VITO	TOMMY
A6	—	ADDED IP RATING	02-NOV-21	RONALD	TOMMY



PART NUMBER CHART	
CAP COLOR	PART NUMBER
BLACK	AHDC169-T-OBDBK
GREEN	AHDC169-T-OBDBGN

NOTES: UNLESS OTHERWISE SPECIFIED

1. COMPATIBLE WITH AHD SERIES 9 POSITION RECEPTACLES.
2. MOISTURE RESISTANCE: IP67 (MATED CONDITION)
3. ALL COMPONENTS ARE RoHS COMPLIANT.
4. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

1	AHDC-09T	TETHER	
1	AHDC-16-9-OBDBK	CAP	
QUANTITY	PART NUMBER	DESCRIPTION	ITEM
MATERIALS LIST			
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = 		SIGNATURES DATE DRAWN: RONALD 02-NOV-21 CHECKED: ORION 03-NOV-21 ENGINEER: APPROVAL: TOMMY 04-NOV-21 CUSTOMER:	
MATERIAL SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.	
PROCESS SPECIFICATIONS:		SIZE TYPE DWG NO. REVISION B C- AHDC169-T-OBDBK A6	
NEXT ASSY:		SCALE: NONE SHEET 1 OF 1	

TITLE: AHD CAP WITH TETHER
DWG NO: AHDC169-T-OBDBK
REV: A6
Sht: 1
Of: 1