

SEARCH BY PART
NUMBER

NEW PRODUCTS

SEARCH BY
CATEGORY

- Pin・Terminal
- Connection terminal
- Socket
- Jumper
- Spacer (Metal type)
- Spacer (Resin type)
- Spacer for SMT
- Power supply
- Contact point・Base
- For high current
- Wiring
- For Panel
- Jack・Plug
- Connector
- For LED
- For Laser diode
- Spring Probe
- Conthrough ®
- Screw・Nut
- Washer
- Bush・Rivet
- Fitting for PCB・Hinge
- Sheet
- Heat dissipation
- Tool


Connection terminal

OWZ-001

**Insertion / removal angle type
(strong type) (Pitch: 2.54 mm)**

RoHS

PDF file



Possible to connect 2PCB in vertical
Pin pitch : 2.54mm. (Max. 20pin connection).

For details, please refer to the PDF file.

Part Number	MOQ
OWZ-001	10



SHINDENKIZAI CO.,LTD.

2-2-13 SOTOKANDA CHIYODA-KU
TOKYO JAPAN 101-0021
TEL +81-3-3253-5539

HOME
PRODUCTS
WORLD PARTNERS
ABOUT US
PRIVACY POLICY



