





ASSEMBLED ISOMETRIC VIEW




TOP VIEW





SIDE VIEW



BOTTOM VIEW



ISOMETRIC VIEW



DETAIL "A"

MATERIALS AND FINISHES:

HOUSING: BLACK ANODIZED ALUMINUM
HEX NUT: STEEL, GOLD PLATED
INTERNAL-TOOTH LOCKWASHER: STEEL, GOLD PLATED
TERMINALS: BRASS HOT TIN PLATED LUG TYPE
O-RING MATERIAL: SILICONE RUBBER
PER: ZZ-R765 CL 2
GRADE 70
O-RING COLOR: BLACK

NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. MOUNTING DIAMETER: Ø15/32"
3. HOLDER ACCEPTS T1-3/4 MIDGET FLANGE BASE LED LAMP.
4. HOLDERS MEET MIL SPEC MIL-L-3661/47
5. MFS470B-WP IS MIL TYPE LH89/1
6. OPERATING VOLTAGE: 2.0-68VDC
7. OPERATING TEMPERATURE: -55C - +85C
8. TIGHTENING TORQUE: 0.5 FT-LBS

REVISION NOTIFICATION	
☐ DLC	
☐ UL/ETL	
☐ MADE IN USA	
☐ CUSTOMER _____	
☐ OTHER _____	
REDLINE CHECKLIST	
☐ REDLINE(YES)	
☐ DATE: _____	
☐ INITIATED BY: _____	
☐ ECR REQUIRED YES ☐ NO ☐	
☐ WORK ORDER# _____	

LED[®]
LEDTRONICS,™ INC.
23105 KASHIWA COURT
TORRANCE, CA 90505

-PROPRIETARY-
This document contains Proprietary
information of LEDTRONICS, INC.
It may not be copied, used or disclosed
for any purpose without the prior express
written consent of LEDTRONICS, INC.

.XXX ± .010 TOLERANCE PER ANSI-Y14.5
.XX ± .025 (UNLESS OTHERWISE STATED)
ANGLES ± 0°,30°
FRACT. ± 1/32

TITLE					
HLDR-MFS470B-WP					
DWG NO		SCALE	SHEET	DATE	
CMHD0032-CUST		1:1	1 OF 1	10-10-08	
CODE IDENT NO.	DWG BY GP	CHK BY	QA RR	MFG PP	R&D LUV
8Z410	10-10-08		12-02-25	12-02-25	12-02-25