


Home > ASLN22211DNG



ASLN22211DNG



Select Quantity

1



Add to Cart

Specifications

Expand All +

Aesthetic Specifications	▾
Electrical Specifications (rated illuminated portion)	▾
Environmental Specifications	▾
Functional Specifications	▾
Mechanical Specifications	▾
Mounting	▾

 PRODUCT DETAILS  SPECIFICATIONS  DOCUMENTS & FILES

Documents and Files

CAD Files Approvals And Standards Technical Document

Name	Last Updated	File Type	File Size	
 ASLN2xxxDNx (2D DXF)	09/19/2025	.DXF	4.80MB	Login to ...
 IGES/OUTSIDE-ASLN2_ASLN3nn	06/24/2024	.IGS	5.21MB	Login to ...
 STEP/OUTSIDE-ASLN2_ASLN3nn	06/24/2024	.STEP	2.51MB	Login to ...
 Parasolid/OUTSIDE-ASLN2_ASLN3nn	06/24/2024	.X_T	1.19MB	Login to ...



IDEC provides industrial control, safety, and automation solutions on a global scale. We offer innovative products and solutions, helping to increase workplace productivity and safety and going beyond to support human well-being.



Support

Contact Us

eCommerce Return Policy

System Integrator Locator

Resources & Documents

Product Cross-Reference

Software Updates

Training

Digital Catalog

Configurator Tool

Compliance Documents

CAD Files

Standards Approved Products

Application Notes

Safety Solutions

Cybersecurity Bulletin

IDEC Corporation Website

About IDEC

Investor Relations 

Offices 

News 

Working at IDEC 

R&D Technology 

IDEC Commitments

Quality Control 

Environment Preservation 

Corporate Social Responsibility 

Join our mailing list for our newsletter!

Enter Email

Sign Up

© 2025 IDEC Corporation

Privacy Policy Terms and Conditions

 USA ▾