


Band adapter straight type for connector of the Serie D38999 Serie III / TV



- On request Bronze and stainless steel

VG Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Nickel-plated	Shell size	D1 max	D2	D3 Tol.	D4 ±0,1	D5 ±0,1	D6 ±0,1	L1 ±0,8
VG95319-1011A001A	TVEGA001-6-09A	TVEGA001-5-09A	09	19,5	M12 x1	9,0 ±0,025	12,8	12,5	13,3	27,0
VG95319-1011A011A	TVEGA011-6-11A	TVEGA011-5-11A	11	23,0	M15 x1	9,5 ±0,2	13,3	13,0	15,8	38,0
VG95319-1011A002A	TVEGA002-6-11A	TVEGA002-5-11A	11	23,0	M15 x1	12,5 ±0,025	16,3	16,0	18,8	27,0
VG95319-1011A012A	TVEGA012-6-13A	TVEGA012-5-13A	13	25,9	M18 x1	9,5 ±0,2	13,3	13,0	15,8	38,0
VG95319-1011A003A	TVEGA003-6-13A	TVEGA003-5-13A	13	25,9	M18 x1	12,0 ±0,025	15,8	15,5	18,3	27,0
VG95319-1011A013A	TVEGA013-6-15A	TVEGA013-5-15A	15	30,2	M22 x1	9,5 ±0,2	13,3	13,0	15,8	38,0
VG95319-1011A004A	TVEGA004-6-15A	TVEGA004-5-15A	15	30,2	M22 x1	13,5 ±0,025	17,3	17,0	19,8	27,0
VG95319-1011A005A	TVEGA004-6-17A	TVEGA005-5-17A	17	33,0	M25 x1	12,8 ±0,025	16,6	16,3	19,1	38,0
VG95319-1011A006A	TVEGA004-6-17A	TVEGA006-5-17A	17	33,0	M25 x1	23,5 ±0,025	27,3	26,9	29,8	38,0
VG95319-1011A014A	TVEGA004-6-19A	TVEGA014-5-19A	19	35,9	M28 x1	17,5 ±0,2	21,3	21,0	23,8	38,0
VG95319-1011A007A	TVEGA004-6-19A	TVEGA007-5-19A	19	35,9	M28 x1	18,0 ±0,025	21,8	21,6	24,3	38,0
VG95319-1011A015A	TVEGA004-6-21A	TVEGA015-5-21A	21	39,2	M31 x1	13,0 ±0,2	16,8	16,5	19,3	38,0
VG95319-1011A016A	TVEGA004-6-21A	TVEGA016-5-21A	21	39,2	M31 x1	16,0 ±0,2	19,8	19,5	22,3	38,0
VG95319-1011A008A	TVEGA004-6-21A	TVEGA008-5-21A	21	39,2	M31 x1	19,0 ±0,025	22,8	22,6	25,3	38,0
VG95319-1011A017A	TVEGA004-6-23A	TVEGA017-5-23A	23	42,4	M34 x1	19,0 ±0,2	22,8	22,5	25,3	38,0
VG95319-1011A009A	TVEGA004-6-23A	TVEGA009-5-23A	23	42,4	M34 x1	23,0 ±0,025	26,8	26,4	29,3	38,0
VG95319-1011A018A	TVEGA004-6-25A	TVEGA018-5-25A	25	45,0	M37 x1	16,0 ±0,2	19,8	19,5	22,3	38,0
VG95319-1011A019A	TVEGA004-6-25A	TVEGA019-5-25A	25	45,0	M37 x1	19,0 ±0,2	22,8	22,5	25,3	38,0
VG95319-1011A020A	TVEGA004-6-25A	TVEGA020-5-25A	25	45,0	M37 x1	22,5 ±0,2	26,3	26,0	28,8	38,0
VG95319-1011A010A	TVEGA004-6-25A	TVEGA010-5-25A	25	45,0	M37 x1	28,5 ±0,025	32,3	32,0	34,8	38,0

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone : +49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_A

ISSUE
B

Band adapter angular type for connector of the Serie D38999 Serie III / TV



- On request Bronze and stainless steel
- Additional measurements and details according form A

VG Part Number Alum inium, Cadmium- plated	AALB Part Number Alum inium, Cadmium-plated	AALB Part Number Alum inium, Nickel- plated	Shell size	L1 max	L2 max	L3 max
VG95319-1011B001A	TVEGB001-6-09A	TVEGB001-5-09A	09	24,0	16,4	31,2
VG95319-1011B002A	TVEGB002-6-11A	TVEGB002-5-11A	11	27,8	18,4	32,8
VG95319-1011B003A	TVEGB003-6-13A	TVEGB003-5-13A	13	29,5	20,0	34,2
VG95319-1011B004A	TVEGB004-6-15A	TVEGB004-5-15A	15	31,9	21,2	36,4
VG95319-1011B005A	TVEGB005-6-17A	TVEGB005-5-17A	17	35,0	22,8	37,8
VG95319-1011B006A	TVEGB006-6-17A	TVEGB006-5-17A	17	37,7	22,8	37,8
VG95319-1011B007A	TVEGB007-6-19A	TVEGB007-5-19A	19	37,4	24,0	39,2
VG95319-1011B008A	TVEGB008-6-21A	TVEGB008-5-21A	21	40,6	25,6	40,9
VG95319-1011B009A	TVEGB009-6-23A	TVEGB009-5-23A	23	43,8	27,1	42,5
VG95319-1011B010A	TVEGB010-6-25A	TVEGB010-5-25A	25	46,3	28,4	43,8

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone :+49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_B

ISSUE
B

SQ adapter for connector of the Serie D38999 Serie III / TV



VG part Number Aluminium, cadmium-plated	AALB Part Number Aluminium, cadmium-plated	AALB Part Number Aluminium, Nickel-plated	Shell size	D1 ±0,2	D2	D5 min.	D7 0 -0,3	D8 +0,5 0	L1 max.	L2 max.	SW 0 -0,2
VG95319-1011C001A	TVEGC001-6-09A	TVEGC001-5-09A	09	19	M12 x1	6,2	12,0	14,0	34,0	16,2	17
VG95319-1011C002A	TVEGC002-6-11A	TVEGC002-5-11A	11	22	M15 x1	7,0	14,0	16,0	35,0	17,2	20
VG95319-1011C003A	TVEGC003-6-11A	TVEGC003-5-11A	11	22	M15 x1	9,5	16,0	18,0	35,0	17,2	20
VG95319-1011C004A	TVEGC004-6-11A	TVEGC004-5-11A	11	22	M15 x1	12,5	20,0	22,0	36,0	18,2	20
VG95319-1011C005A	TVEGC005-6-13A	TVEGC005-5-13A	13	25	M18 x1	9,5	16,0	18,0	35,0	17,2	23
VG95319-1011C006A	TVEGC006-6-15A	TVEGC006-5-15A	15	29	M22 x1	12,5	20,0	22,0	36,0	18,2	27
VG95319-1011C007A	TVEGC007-6-15A	TVEGC007-5-15A	15	29	M22 x1	9,5	16,0	18,0	36,0	18,2	27
VG95319-1011C008A	TVEGC008-6-15A	TVEGC008-5-15A	15	29	M22 x1	15,5	23,0	25,0	36,0	18,2	27
VG95319-1011C009A	TVEGC009-6-17A	TVEGC009-5-17A	17	32	M25 x1	15,5	23,0	25,0	36,0	18,2	30
VG95319-1011C010A	TVEGC010-6-17A	TVEGC010-5-17A	17	32	M25 x1	7,0	14,0	16,0	35,0	17,2	30
VG95319-1011C011A	TVEGC011-6-19A	TVEGC011-5-19A	19	36	M28 x1	18,5	24,5	28,0	36,0	18,2	34
VG95319-1011C012A	TVEGC012-6-21A	TVEGC012-5-21A	21	39	M31 x1	21,5	28,5	32,0	36,0	18,2	37
VG95319-1011C013A	TVEGC013-6-23A	TVEGC013-5-23A	23	43	M34 x1	23,5	30,5	34,0	36,0	18,2	41
VG95319-1011C014A	TVEGC014-6-23A	TVEGC014-5-23A	23	43	M34 x1	15,5	23,0	25,0	36,0	18,2	41
VG95319-1011C015A	TVEGC015-6-25A	TVEGC015-5-25A	25	46	M37 x1	27,5	34,0	38,0	36,0	18,2	44

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone : +49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_C

ISSUE
B

Band adapter straight type for connector of the Serie D38999 Serie III / TV



VG Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Nickel-plated	Shell size	D1 ±0,2	D2	D6 +0,5 0	D7 ±0,1	D8 0 -0,15	D9 ±0,1	L1 max	SW 0 -0,2
VG95319-1011D001A	TVEGD001-6-09A	TVEGD001-5-09A	09	19	M12 x 1	19,0	22,5	23,3	24,5	32,0	17
VG95319-1011D002A	TVEGD002-6-11A	TVEGD002-5-11A	11	22	M15 x 1	9,5	13,0	13,8	15,0	30,0	20
VG95319-1011D003A	TVEGD003-6-11A	TVEGD003-5-11A	11	22	M15 x 1	22,0	24,8	25,6	28,3	32,0	20
VG95319-1011D004A	TVEGD004-6-13A	TVEGD004-5-13A	13	25	M18 x 1	25,0	28,5	29,3	32,0	32,0	23
VG95319-1011D005A	TVEGD005-6-15A	TVEGD005-5-15A	15	29	M22 x 1	15,5	19,0	19,8	21,0	30,0	27
VG95319-1011D006A	TVEGD006-6-15A	TVEGD006-5-15A	15	29	M22 x 1	17,5	21,0	21,8	23,0	30,0	27
VG95319-1011D007A	TVEGD007-6-17A	TVEGD007-5-17A	17	32	M25 x 1	28,5	32,0	32,8	35,5	32,0	30
VG95319-1011D008A	TVEGD008-6-19A	TVEGD008-5-19A	19	36	M28 x 1	22,0	24,8	25,6	28,3	31,0	34
VG95319-1011D009A	TVEGD009-6-21A	TVEGD009-5-21A	21	39	M31 x 1	25,0	28,5	29,3	32,0	34,0	37
VG95319-1011D010A	TVEGD010-6-23A	TVEGD010-5-23A	23	43	M34 x 1	12,7	16,5	17,0	18,2	34,0	41
VG95319-1011D011A	TVEGD011-6-25A	TVEGD011-5-25A	25	46	M37 x 1	17,5	21,0	21,8	23,0	34,0	44

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone : +49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_D

ISSUE
B

Shrink boot adapter straight for connector of the Serie D38999 Serie III / TV



VG Part Number	AALB Part Number	AALB Part Number	Shell size	D1	D2	D4	D7	D8	L1
Aluminium, Cadmium-plated	Aluminium, Cadmium-plated	Aluminium, Nickel-plated		±0,2		+0,2 -0	0 -0,2	+0,5 0	max
VG95319-1011E001	TVEGE001-5-09A	TVEGE001-6-09A	09	19	M12 x 1	8,65	12,0	14,0	33,0
VG95319-1011E002	TVEGE002-5-11A	TVEGE002-6-11A	11	22	M15 x 1	12,0	14,0	16,0	33,0
VG95319-1011E003	TVEGE003-5-13A	TVEGE003-6-13A	13	25	M18 x 1	13,8	16,0	18,0	33,0
VG95319-1011E004	TVEGE004-5-15A	TVEGE004-6-15A	15	29	M22 x 1	16,8	20,0	22,0	33,0
VG95319-1011E005	TVEGE005-5-17A	TVEGE005-6-17A	17	32	M25 x 1	19,8	23,0	25,0	33,0
VG95319-1011E006	TVEGE006-5-19A	TVEGE006-6-19A	19	36	M28 x 1	22,8	24,5	28,0	33,0
VG95319-1011E007	TVEGE007-5-21A	TVEGE007-6-21A	21	39	M31 x 1	25,8	28,5	32,0	33,0
VG95319-1011E008	TVEGE008-5-23A	TVEGE008-6-23A	23	43	M34 x 1	26,8	30,5	34,0	33,0
VG95319-1011E009	TVEGE009-5-25A	TVEGE009-6-25A	25	46	M37 x 1	30,8	34,5	38,0	33,0

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone :+49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_E

ISSUE
B

SQ adapter for connector of the Serie D38999 Serie III / TV



VG Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Nickel-plated	Shell size	D1 ±0,2	D2	D4 +0,2 -0	D7 ±0,5	D8 0 -0,2	D9 +0,5 0	L1 ±0,5	L2 0 -1	L3 ±0,5	SW 0 -0,2
VG95319-1011F001	TVEGF001-6-09A	TVEGF001-5-09A	09	22,0	M12 x 1	6,2	14,0	19,0	21,0	23,0	18,0	16,0	20
VG95319-1011F002	TVEGF002-6-11A	TVEGF002-5-11A	11	25,0	M15 x 1	7,0	16,0	22,0	24,0	23,0	18,0	16,0	23
VG95319-1011F003	TVEGF003-6-13A	TVEGF003-5-13A	13	29,0	M18 x 1	9,5	18,0	25,5	28,0	24,0	19,0	17,0	27
VG95319-1011F004	TVEGF004-6-13A	TVEGF004-5-13A	13	29,0	M18 x 1	15,5	25,0	25,5	28,0	23,0	18,0	16,0	27
VG95319-1011F005	TVEGF005-6-15A	TVEGF005-5-15A	15	32,0	M22 x 1	12,5	22,0	29,0	32,0	24,0	19,0	17,0	30
VG95319-1011F006	TVEGF006-6-15A	TVEGF006-5-15A	15	32,0	M22 x 1	15,5	25,0	29,0	32,0	24,0	19,0	17,0	30
VG95319-1011F007	TVEGF007-6-17A	TVEGF007-5-17A	17	36,0	M25 x 1	15,5	25,0	32,5	36,0	24,0	19,0	17,0	34
VG95319-1011F008	TVEGF008-6-19A	TVEGF008-5-19A	19	39,0	M28 x 1	18,5	28,0	35,5	39,0	24,0	19,0	17,0	37
VG95319-1011F009	TVEGF009-6-19A	TVEGF009-5-19A	19	39,0	M28 x 1	15,5	25,0	35,5	39,0	25,0	20,0	18,0	37
VG95319-1011F010	TVEGF010-6-21A	TVEGF010-5-21A	21	42,0	M31 x 1	21,0	32,0	38,5	42,0	24,0	19,0	17,0	40
VG95319-1011F011	TVEGF011-6-23A	TVEGF011-5-23A	23	45,0	M34 x 1	23,5	34,0	42,0	45,5	24,0	19,0	17,0	43
VG95319-1011F012	TVEGF012-6-25A	TVEGF012-5-25A	25	49,0	M37 x 1	27,5	38,0	45,5	49,0	24,0	19,0	17,0	47

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone : +49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_F

ISSUE
B

Band adapter straight type for connector of the Serie D38999 Serie III / TV



- On request Bronze and stainless steel
- Additional measurements and details according form A

VG Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Cadmium-plated	AALB Part Number Aluminium, Nickel-plated	Shell size	D7 ±0,2	SW 0 -0,2
VG95319-1011G001A	TVEGG001-6-09A	TVEGG001-5-09A	09	19,0	17
VG95319-1011G011A	TVEGG011-6-11A	TVEGG011-5-11A	11	22,0	20
VG95319-1011G002A	TVEGG002-6-11A	TVEGG002-5-11A	11	22,0	20
VG95319-1011G012A	TVEGG012-6-13A	TVEGG012-5-13A	13	25,0	23
VG95319-1011G003A	TVEGG003-6-13A	TVEGG003-5-13A	13	25,0	23
VG95319-1011G013A	TVEGG013-6-15A	TVEGG013-5-15A	15	29,0	27
VG95319-1011G004A	TVEGG004-6-15A	TVEGG004-5-15A	15	29,0	27
VG95319-1011G005A	TVEGG005-6-17A	TVEGG005-5-17A	17	32,0	30
VG95319-1011G006A	TVEGG006-6-17A	TVEGG006-5-17A	17	32,0	30
VG95319-1011G014A	TVEGG014-6-19A	TVEGG014-5-19A	19	36,0	34
VG95319-1011G007A	TVEGG007-6-19A	TVEGG007-5-19A	19	36,0	34
VG95319-1011G015A	TVEGG015-6-21A	TVEGG015-5-21A	21	39,0	37
VG95319-1011G016A	TVEGG016-6-21A	TVEGG016-5-21A	21	39,0	37
VG95319-1011G008A	TVEGG008-6-21A	TVEGG008-5-21A	21	39,0	37
VG95319-1011G017A	TVEGG017-6-23A	TVEGG017-5-23A	23	43,0	41
VG95319-1011G009A	TVEGG009-6-23A	TVEGG009-5-23A	23	43,0	41
VG95319-1011G018A	TVEGG018-6-25A	TVEGG018-5-25A	25	46,0	44
VG95319-1011G019A	TVEGG019-6-25A	TVEGG019-5-25A	25	46,0	44
VG95319-1011G020A	TVEGG020-6-25A	TVEGG020-5-25A	25	46,0	44
VG95319-1011G010A	TVEGG010-6-25A	TVEGG010-5-25A	25	46,0	44

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone :+49 (0)6831/9810-0 Fax : 9810-20


DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011_FORM_G

ISSUE
B

Band adapter angular type for connector of the Serie D38999 Serie III / TV



- On request Bronze and stainless steel
- Additional measurements and details according form A

VG Part Number	AALB Part Number	AALB Part Number	Shell size	L1	L2	L3	SW
Aluminium, Cadmium-plated	Aluminium, Cadmium-plated	Aluminium, Nickel-plated		max	max	max	
VG95319-1011H001A	TVEGH001-6-09A	TVEGH001-5-09A	09	24,0	16,4	31,2	17
VG95319-1011H002A	TVEGH002-6-11A	TVEGH002-5-11A	11	27,8	18,4	32,8	20
VG95319-1011H003A	TVEGH003-6-13A	TVEGH003-5-13A	13	29,5	20,0	34,2	23
VG95319-1011H004A	TVEGH004-6-15A	TVEGH004-5-15A	15	31,9	21,2	36,4	27
VG95319-1011H005A	TVEGH005-6-17A	TVEGH005-5-17A	17	35,0	22,8	37,8	30
VG95319-1011H006A	TVEGH006-6-17A	TVEGH006-5-17A	17	37,7	22,8	37,8	30
VG95319-1011H007A	TVEGH007-6-19A	TVEGH007-5-19A	19	37,4	24,0	39,2	34
VG95319-1011H008A	TVEGH008-6-21A	TVEGH008-5-21A	21	40,6	25,6	40,9	37
VG95319-1011H009A	TVEGH009-6-23A	TVEGH009-5-23A	23	43,8	27,1	42,5	41
VG95319-1011H010A	TVEGH010-6-25A	TVEGH010-5-25A	25	46,3	28,4	43,8	44

AALB-G

Am Kleinbahnhof 4 D-66740 SAARLOUIS
Phone :+49 (0)6831/9810-0 Fax : 9810-20

DESIGNED: G.CHAMPLON
DATE : 27.07.2016

CHECKED:
APPROVED:

Ref.:VG95319-1011-FORM_H

ISSUE
B