

Product data sheet

Subminiature connectors




Product description	Snap-In Female cable connector, Contacts: 4, 2.5-4.0 mm, unshielded, solder, IP40
Area	Snap-In IP40
Series	719
Part no.	09 9764 70 04


Illustration (may vary)



Scale drawing



Contact arrangement (Plug-in side)



You can find the assembly instructions on the next page.

Technical data

General features

Part no.	09 9764 70 04
Connector design	Female cable connector
Version	Connector socket straight
Connector locking system	snap-in
Termination	solder
Degree of protection	IP40
Connection cross-section	0.25 mm ² / AWG 24
Cable outlet	2.5-4.0 mm
Temperature range from/to	-25 °C / 70 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	1.30
Customs tariff number	85369010
Country of Origin	DE

Electrical parameters

Rated voltage	60 V
Rated impulse voltage	800 V
Rated current	3,0 A
Insulation resistance	≥ 10 ¹⁰ Ω
Pollution degree	1
Overvoltage category	II
Insulating material group	III
EMC compliance	unshielded

Product data sheet

Subminiature connectors



Product description	Snap-In Female cable connector, Contacts: 4, 2.5-4.0 mm, unshielded, solder, IP40
Area	Snap-In IP40
Series	719
Part no.	09 9764 70 04

Material

Housing material	PA
Contact body material	PA
Contact material	CuSn (bronze)
Contact plating	Au (gold)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	1cd87190-69a5-4173-a40a-55fa1fb0a094

Classifications

eCl@ss 11.1	27-44-01-09
ETIM 9.0	EC003569

Declarations of conformity

Low Voltage Directive	EN 60529:1991 EN 60204-1:2018
-----------------------	---------------------------------

Trade-Compliance

Copper (9903.78.01)	0.000346 kg
---------------------	-------------

Assembly instructions

1. Bead pressing screw and clamping sleeve to cable.

2. Dismantle cable to 9 mm length.

3. Strip and solder single wires.

4. Screw on clamping sleeve.

5. Tighten pressing screw.

female insert

male insert

9

3

strip

dismantle

clamping sleeve

pressing screw

0,2 Nm

0,8-1,0 Nm

Date: 11.08.2026

Downloaded from [Arrow.com](https://arrow.com)

Product description	Snap-In Female cable connector, Contacts: 4, 2.5-4.0 mm, unshielded, solder, IP40
Area	Snap-In IP40
Series	719
Part no.	09 9764 70 04

General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".