


Female Header Micro Match SMD 1,27 mm

Series

374




Rated current	1,0 A
Rated voltage	230 V _{RMS} / V _{DC}
Withstand voltage	500 V _{RMS} for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +125°C
Max. processing temper.	260°C for 10 seconds

pitch	1,27
termination	
max. pincount	026

All dimensions in mm.


Variation

Without locking feature





1

With locking feature



2

PCB Layout



no. of contacts	see figure left	see figure left	see figure left	available in variation
n	A	B	C	
004	7,00	3,81	5,60	1
006	9,54	6,35	8,14	1
008	12,08	8,89	10,68	1
010	14,62	11,43	13,22	1
012	17,16	13,97	15,76	1
014	19,70	16,51	18,30	1
016	22,24	19,05	20,84	1
018	24,78	21,59	23,38	1
020	27,32	24,13	25,92	1
022	29,86	26,67	28,46	1
024	32,40	29,21	31,00	1
026	34,94	31,75	33,54	1
004	9,70	3,81	5,60	2
006	12,24	6,35	8,14	2
008	14,78	8,89	10,68	2
010	17,32	11,43	13,22	2
012	19,86	13,97	15,76	2
014	22,40	16,51	18,30	2
016	24,94	19,05	20,84	2
018	27,48	21,59	23,38	2
020	30,02	24,13	25,92	2
022	32,56	26,67	28,46	2
024	35,10	29,21	31,00	2
026	37,64	31,75	33,54	2

Plating:
T = Sn

Packaging:
R = Reel
T = Tube

Cap:
0 = Without cap
1 = With cap

Variation (1,2)

No. of contacts

Plating contact

Packaging (R,T)

Cap (0,1)

mpe
GARRY

www.mpe-connector.de

Order code:

374-?-?-?-?-0-NTX-K??

Mating series	373	372
see page	3-19	6-5

Product group
4

CS280814_V4