

Johanson Part Number Information

08-02-
2023

Johanson Part Number:	LRC0603CJ27NGV001T	Johanson Company:	Johanson Technology Inc.
Legacy P/N:	L-14C27NJV4T	NCNR:	No
Description:	Ceramic Inductor, 0603, 27nH±5%, 300mA, Ni/Sn (RoHS), No Mark, 7" Reel Paper Tape	Thickness (Max):	0.039
		Thickness (Min):	0.023
Life Cycle Stage:	Active - Production	End Band (Max):	0.016
AEC Q200 Qualified:	No	Standard Item:	No
Schedule B:	8504.50.0000	Lead Time Typical (Weeks)*:	
Harmonization Code:	8504.50.40.00	*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.	14
ITAR:	No	Length (Min):	0.057
ECCN:	EAR99	Length (Max):	0.069
RoHS Compliance:	Yes, RoHS 10/10	Width (Min):	0.023
REACH:	Yes	Width (Max):	0.039
Country of Origin:	TW	Part Weight (mg):	3.980
Product Family:	Inductors	Packaged Weight (lb) Arm:	0.300
Product Subfamily:	Ceramic Inductors	Packaging:	7" Reel Paper Tape
Tolerance:	±5%	Packaging Qty:	4000
Termination:	Ni/Sn (RoHS)	Operating Temp Range:	-40°C to + 100°C
Marking:	No Mark	Storage Temp Range (Packaged):	-10°C to +40°C
Product Release Date:	04 January, 2006	Storage Temp Range (Non Operating):	-40°C to +125°C
Web Page Link:	Download this information page 		
	https://www.johansontechnology.com/ceramic-inductors		

- QUICK LINKS
- ▶ Home

▶ About

▶ Contact Us

▶ News

▶ Do Not Sell My Personal Information



VISIT OUR SISTER SITE:

JOHANSON
DIELECTRICS



Johanson Technology is dedicated to providing the highest level of customer satisfaction through high quality components, superior customer service and forward looking, advanced products.