


"Stay Connected" with



HEYware Products

a PennEngineering® Company











Heyco® Nytye® Push Mount Nylon Cable Ties

PART SPECIFICATIONS				PART NO.			DESCRIPTION	PART DIMENSIONS												STYLE
Tensile Strength		Max. Bundle Diameter		Natural	UV Black	Heat Stabilized UV Black		A		B		C		Panel Thickness		Mounting Hole Dia.				
Lbs.	N	in.	mm.					Length	mm.	Width	mm.	Spacer Height	in.	mm.	in.	mm.	in.	mm.	in.	
Tension Wings																				
40	178	1.42	36,0	-	-	3907	PMWS-155-HSB	6.23	158	.14	3,5	-	-	.031 - .093	0,8 - 2,4	.187	4,7	1		
50	222	1.57	40,0	13254	13254B	-	PMT-50-070	7.09	180	.19	4,8	-	-	.031 - .093	0,8 - 2,4	.187	4,7	2		
		1.75	44,5	3904	3905	3903B	PMT 150	8.00	203	.19	4,8	-	-	.000 - .125	0,0 - 3,2	.250	6,4	1		
Tension Wings, Standoff																				
18	80	.75	19,1	13262	13262B	-	PMST-18-050-156	5.04	128	.10	2,5	.24	6,1	.031 - .078	0,8 - 2,0	.156	4,0	3		
40	178	1.38	35,0	13267	13267B	-	PMST-40-066-197	6.69	170	.14	3,6	.51	13,0	.031 - .078	0,8 - 2,0	.197	5,0			
		1.25	31,8	13268	13268B	-	PMST-40-068-187	6.81	173	.14	3,6	.78	19,8	.031 - .078	0,8 - 2,0	.187	4,7			
50	222	.98	25,0	13269	-	13269B	PMST-50-063-259	6.34	161	.19	4,8	.54	13,7	.027 - .118	0,7 - 3,0	.259	6,6	7		
Cupped Base, Standoff, Releasable																				
30	133	1.25	31,8	13273	13273B	-	PMRS-30-066	6.63	168	.14	3,6	.53	13,5	.023 - .098	0,6 - 2,5	.236 - .255	6,0 - 6,5	4		
Blind Mount - 2PC*																				
50	222	2.13	54,1	13285	13285B	23285B	PMBMT-50-079-5	7.87	200	.19	4,8	-	-	.031 - .197	0,8 - 5,0	.177 - .197	4,5 - 5,0	5		
				13286	13286B	23286B	PMBMT-50-079-7	7.87	200	.19	4,8	-	-	.031 - .276	0,8 - 7,0	.256 - .276	6,5 - 7,0			
				-	13281B***	-	PMBMDLT-50-079-7	8.66	220	.19	4,8	-	-	.031 - .276	0,8 - 7,0	.256 - .276	6,5 - 7,0	***		
Blind Mount - 1PC**																				
50	222	1.97	50,0	13288	13288B	23288B	PMBMT-50-081-71	8.11	206	.19	4,8	-	-	.031 - .281	0,8 - 7,1	.250 - .270	6,4	6		

Standard color natural and UV Black. Consult Heyco for other colors.

*Discrete blind mount fastener is pre-assembled to the Nytye. **Constructed so that the discrete blind mount fastener is molded to the Nytye.

***2-Piece Blind Mount with Double Loop Cable Tie, see page 7-65 for other Double Loop Cable Ties



***Double Loop Configuration

Quick
Specs

Material	Nylon 6/6, Nylon 6/6 UV Black, or Nylon 6/6 Heat Stabilized/UV Black
Flammability Rating	94V-2
Temperature Range	Nylon 6/6 and Nylon 6/6 UV Black: -40°F (-40°C) to 185°F (85°C) Nylon 6/6 Heat Stabilized/UV Black: -40°F (-40°C) to 221°F (105°C)