

# EuropacPRO Side Panel for Stainless Steel Gasket, Type H, Handle Holes, 3 U, 175 mm

## CATALOG NUMBER

24567-125



Combinations of horizontal rails and side panels

|                 |         | "H" can be combined. "T" combinations not recommended |            |           |            |
|-----------------|---------|-------------------------------------------------------|------------|-----------|------------|
| Horizontal rail | 19" EIA | -                                                     | +          | +         | +          |
|                 | 19" EIA | +                                                     | +          | +         | +          |
|                 | 19" EIA | +                                                     | +          | -         | -          |
|                 | 19" EIA | +                                                     | +          | -         | -          |
| Side panel      |         | Light 1.1                                             | Flexibel 2 | Heavy 3.0 | Rugged 4.0 |
|                 |         | Light 1.1                                             | Flexibel 2 | Heavy 3.0 | Rugged 4.0 |

Side panel

Side Panel, Type H, with handle holes, tox welded to the 19" bracket for stainless steel gasket.

## CERTIFICATIONS



## FEATURES

For high mechanical demands, 19" bracket, tox-cold welded, Al, 2 mm, clear passivated, front anodized

Versions for EMC sealing (stainless steel or textile)

## PRODUCT ATTRIBUTES

Rack Height: 3U

Package Quantity: 2

Finish: Anodized; Passivated

Material: Aluminum

Product Family: EuropacPRO

Product Type: Side Panel

Type: Type H

Works With: Subracks

Gross Weight: 0.398kg

## ADDITIONAL PRODUCT DETAILS

Side panel and 19" bracket are tox-cold welded together. token = Clinching technique, without add aids. This takes place with special tools and high pressure.

Please order front handles separately.

9 U version available on request.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**