

Type 4X Stainless Steel Wallmount Enclosure *HWSSHK Series*

Hinge Door with Handle



**Panel
Sold
Separately**



Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for wallmount applications.
- Provides high level of protection where equipment is hosed down or otherwise be exposed to wet conditions where corrosion is a serious problem.
- Ideal for processing plants, utility, outdoor municipal or petro chemical locations where easy yet secure access is required.

Standards

- UL 508A Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- Complies with
 - NEMA 3R, 4, 4X, 12 and 13
 - IEC 60529, IP 66

Construction

- Formed 14 gauge 304 or 316 stainless steel.
- Continuously welded seams ground smooth.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- 316 Stainless pad lockable handle with 3 point roller latching system secures door.
- Stainless steel continuous hinge on door may be removed by pulling the stainless steel hinge pin
- Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Bonding stud provided on door and grounding stud installed in enclosure.

Finish

- Cover and enclosure are natural stainless steel with smooth brushed finish.

Accessories

- Additional Inner Panels
- Type 12/4, 4X Handle Kits
- Door Stop Kit
- Floor Stand Kit
- Climate Control
- General Accessories
- Perforated Inner Panels
- Swing Panel Kit
- Drip Shield Kit
- Window Kits
- Lighting

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

304 S.S. Part No.	316 S.S. Part No.	Enclosure			Optional Inner Panel		
		H	W	D	Part No.	H	W
HW24206SSH K	HW24206S16H K	24.00	20.00	6.00	18P2117	21.00	17.00
HW24246SSH K	HW24246S16H K	24.00	24.00	6.00	18P2121	21.00	21.00
HW24168SSH K	HW24168S16H K	24.00	16.00	8.00	18P2113	21.00	13.00
HW24208SSH K	HW24208S16H K	24.00	20.00	8.00	18P2117	21.00	17.00
HW24248SSH K	HW24248S16H K	24.00	24.00	8.00	18P2121	21.00	21.00
HW24308SSH K	HW24308S16H K	24.00	30.00	8.00	18P2721	21.00	27.00
HW30208SSH K	HW30208S16H K	30.00	20.00	8.00	18P2717	27.00	17.00
HW30248SSH K	HW30248S16H K	30.00	24.00	8.00	18P2721	27.00	21.00
HW30308SSH K	HW30308S16H K	30.00	30.00	8.00	18P2727	27.00	27.00
HW36248SSH K	HW36248S16H K	36.00	24.00	8.00	18P3321	33.00	21.00
HW36308SSH K	HW36308S16H K	36.00	30.00	8.00	18P3327	33.00	27.00
HW42368SSH K	HW42368S16H K	42.00	36.00	8.00	18P3933	39.00	33.00
HW48368SSH K	HW48368S16H K	48.00	36.00	8.00	18P4533	45.00	33.00
HW242010SSH K	HW242010S16 HK	24.00	20.00	10.00	18P2117	21.00	17.00
HW302410SSH K	HW302410S16 HK	30.00	24.00	10.00	18P2721	27.00	21.00
HW362410SSH K	HW362410S16 HK	36.00	24.00	10.00	18P3321	33.00	21.00
HW363010SSH K	HW363010S16 HK	36.00	30.00	10.00	18P3327	33.00	27.00
HW423010SSH K	HW423010S16 HK	42.00	30.00	10.00	18P3927	39.00	27.00
HW483610SSH K	HW483610S16 HK	48.00	36.00	10.00	18P4533	45.00	33.00
HW242412SSH K	HW242412S16 HK	24.00	24.00	12.00	18P2121	21.00	21.00
HW302412SSH K	HW302412S16 HK	30.00	24.00	12.00	18P2721	27.00	21.00
HW363012SSH K	HW363012S16 HK	36.00	30.00	12.00	18P3327	33.00	27.00
HW363612SSH K	HW363612S16 HK	36.00	36.00	12.00	18P3333	33.00	33.00
HW423612SSH K	HW423612S16 HK	42.00	36.00	12.00	18P3933	39.00	33.00
HW483612SSH K	HW483612S16 HK	48.00	36.00	12.00	18P4533	45.00	33.00
HW603612SSH K	HW603612S16 HK	60.00	36.00	12.00	18P5733	57.00	33.00
HW302416SSH K	HW302416S16 HK	30.00	24.00	16.00	18P2721	27.00	21.00
HW363016SSH K	HW363016S16 HK	36.00	30.00	16.00	18P3327	33.00	27.00
HW483616SSH K	HW483616S16 HK	48.00	36.00	16.00	18P4533	45.00	33.00
HW603616SSH K	HW603616S16 HK	60.00	36.00	16.00	18P5733	57.00	33.00

Alternative inner panel options also available.

Tags: **Type 4X, Type 12, stainless steel, outdoor, corrosion, industrial, petro chemical, processing, utility** *Data subject to change without notice.*

© 2026. Hammond Manufacturing Ltd. All rights reserved.