



Part Number : [1300530004](#)
Product Description : Brad RJ-Lnxx Direct PCB
Mount Ethernet Receptacle, 1" - 14 UNC Threads
Series Number : 130053
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : ENPR1FF5

Documents and Resources

Drawings

[1300530004_sd.pdf](#)
[Symbol and Footprint \(Multi-Format\)](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130053
Description	Brad RJ-Lnxx Direct PCB Mount Ethernet Receptacle, 1" - 14 UNC Threads
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Brad,RJ-Lnxx
Type	PCB Mount
UPC	78678846636

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V DC

Physical

Coupling Type	External Thread
Gender	Female
Keyway	None
Length	N/A
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Orientation	Straight
Panel Mount	N/A
Poles	N/A
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A

Wire Size (AWG)	N/A
-----------------	-----

This document was generated on Sep 21, 2026