



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	3/23/11	D.GRIFFIN
B	ECN 7561: ADDED PANEL CUTOUT, UPDATED ROHS AND FORMAT	8/20/14	D. CASTRO




RJ45 (8X8) FEMALE
SHIELDED CONNECTOR



ABS
(BLACK)

RJ45 (8X8) FEMALE
SHIELDED CONNECTOR



Ø 1.004
[25.50]

RECOMMENDED
PANEL CUTOUT

PANEL THICKNESS:

.125" MAX WITH GASKET
.187" MAX WITHOUT GASKET
.062" MIN

NOTES:

- INGRESS PROTECTION RATING IP67
- COMPONENT SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPEC. PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13]	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845		CATEGORY TELECOM/MODULAR
	DRAWN BY D. CASTRO	3/23/11			
	CHECKED BY D. PARHAM	3/23/11	PRODUCT DESCRIPTION ENET FR/FR PASS-THRU SHLD		
	APPROVED BY J. RUST	3/23/11			
	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	REV. B			
	COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321	DWG. NO. WJP1F5	
		SCALE: NONE CAD FILE: WJP1F5.SLDDRW			SHEET 1 OF 1