



NC3FM-C-B

World's first 3 pole unisex XLR cable connector,
black

Features & Benefits

- ✓ World's first unisex XLR
- ✓ 3 pole male and female cable connector in one housing
- ✓ Easy selectable gender - converted by sliding housing back and forth
- ✓ Substitute adapters, ideal as an emergency kit
- ✓ With all benefits of the XLR XX series

Technical Information

Product	
Title	NC3FM-C-B
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	≤ 4 pF
Contact resistance	≤ 3 mΩ
Dielectric strength	1.5 kVdc
Insulation resistance	> 2 GΩ (initial)
Rated current per contact	16 A
Rated voltage	<50 V

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	max. 2.5 mm²
Wiresize	max. 14 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	0.2 µm Au
Contacts	Brass (CuZn39Pb3) (male)
Insert	Polyamdie (PA 6.6 30 % GR)
Locking element	Zinc diecast (ZnAl4Cu1) / Ck 67 (spring)
Shell	Black chromium
Shell plating	Nickel
Strain relief	Polyacetal (POM)

Environmental	
Flammability	UL 94 HB
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C