



Full Cycle Ratchet Crimper, #22-10 AWG Bare

By Burndy
Catalog # [MR20](#)

Full Cycle Ratchet Crimper, #22-10 AWG Uninsulated (Bare) Terminals & Splices

Features

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Application

Crimping

Specifications

Standards - RoHS Compliance	EX
Status	
Buy American Compliant	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)

Conductor

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Dimensions

Package Height	0.000 in
Length	8.88 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Weight	1.1 lb.
Height	2.5 in
Width	6 in
Dimensions	8.88 in x 6 in x 2.5 in

General

Application - For Use On	Uninsulated Terminals and Splices
Trade Name	HYTOOL™
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Product Type	MR10, 15, 18, 22, & 25
Die Type	Permanent Die Grooves
UPC	781810011195
UPC 12 Digit	781810011195
UPC 14 Digit GTIN	00781810011195

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only
Carton Quantity	20

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)