



Fan Accessories




SUNON®

METAL FINGER GUARD


FG-02 For 25mm Fan




FG-03 For 30mm Fan




FG-04 For 40mm Fan




FG-05 For 50mm Fan




FG-06 For 60mm Fan




FG-08 For 80mm Fan




FG-09 For 92mm Fan




FG-12 For 120mm Fan




FG-17A For 172mm Fan




FG-17B For 172mm Fan




FG-18A For 176mm Fan



FG-18B For 176mm Fan




FG-25 For 254mm Fan




METAL FILTER GUARD


FM 06 For 60mm Fan




FM 08 For 80mm Fan



FM 09 For 92mm Fan




FM 12 For 120mm Fan




PLASTIC GUARD


PB-06 For 60mm Fan




PB-08 For 80mm Fan




PB-09 For 92mm Fan




PB-12 For 120mm Fan






PB-17 For 170mm Fan






PLASTIC FILTER GUARD






For 60mm Fan(06 D Type)






For 80mm Fan(08 D Type)



For 120mm Fan(12 D Type)




For 172mm Fan(17 D Type)




AC CORD

Power cord with straight connector





A2-03	300mm Length
A2-06	600mm Length
A2-10	1000mm Length
A2-20	2000mm Length



B2-03	300mm Length
B2-06	600mm Length
B2-10	1000mm Length
B2-20	2000mm Length




C2-03	300mm Length
C2-06	600mm Length
C2-10	1000mm Length
C2-20	2000mm Length



AC CORD


A3-A

(unit : mm)




B2-C

(unit : mm)




A3-B

(unit : mm)



C2-D

(unit : mm)



Headquarters:

Sunonwealth Electric Machine Industry Co., Ltd.

No. 30, Lane 296, Hsin Ya Road, Chien-Chen District, Kaohsiung, Taiwan

TEL : +886-7-8135888

FAX : +886-7-8230505/8230606/8231010

URL: <http://www.sunon.com>

E-mail: sunon@email.sunon.com.tw

Sunon Inc. (U.S.A.)

1075 West Lambert Road Suite A, Brea, California 92821, U.S.A

TEL : +1-714-255-0208

FAX : +1-714-255-0802

URL : <http://www.sunonusa.com>

E-mail : info@sunon.com

Sunon SAS (Europe)

Parc Medicis, 66, Ave Des Pepinieres 94832, Fresnes Cedex-France

TEL : +33-1-46154515

FAX : +33-1-46154510

URL: <http://www.sunoneurope.com>

E-mail : info@sunoneurope.com

Sunon Corporation (Japan)

Stork Minami Otsuka 4Fl.33-1, 2 Chome,
Minami Otsuka Toshimaku, Tokyo, Japan 170-0005

TEL : +81-3-5395-3069

FAX: +81-3-5395-3080

URL: <http://www.sunon.co.jp>

E-mail : info@sunon.co.jp

Sunonwealth Electric Machine Industry (HK) Ltd. (Hong Kong)

1906 Nan Fung Center, 264 Castle Peak Road, Tsuen Wan, Hong Kong

TEL : + 852-24-111-388

FAX : + 852-24-050-707

E-mail : info@sunon.com.hk

Sunon Technologies Pte Ltd. (Singapore)

10 Toh Guan Road, #03-08 TT International Tradepark, Singapore 608838

TEL : +65-6795-0300

FAX : +65-6795-0600

E-mail : info@sunon.com.sg

Sunon Electronics (Kun Shan) Co.,Ltd. (Shanghai, China)

TEL : +86-512-57700108

FAX : +86-512-57711575

Sunon China (Shen Zhen) Office (Shen Zhen, China)

TEL : +86-755-26880688

FAX : +86-755-26880288

E-mail : info@sunon.com.cn