

Product Line

- [DeepTronica](#) >
- [Single Pair Ethernet](#) >
- [ZConnect](#) >
- [Ceres](#) >
- [X-Lok](#) >
- [Accessory](#)
- [Middle Size](#)
- [Mini Size](#)
- [Large Size](#)
- [Standard Size](#)
- [M Series](#) >
- [FLOS & FLOS+](#) >
- [Power](#) >
- [RBL](#) >
- [HS-Lok](#) >
- [NMEA 2000](#) >
- [Heavy Duty Shielded](#) >
- [RJ](#) >
- [USB](#) >
- [SSL](#) >
- [HDMI](#) >
- [DVI](#) >
- [Fiber Optic](#) >
- [RF](#) >
- [Cable Joiner](#) >
- [Cable Gland](#) >
- [Pressure Relief Vent](#) >
- [LED Light Guide](#) >
- [D-Sub](#) >



BB-02BFFA-QL8SPP

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: N/A
Certificate: UL1977

You must login first for view the price

Quantity Check Stock

Add to Cart Inquiry

Can't find? [Customize your part](#)

Mating Pair & Accessories

Search

☐

☐

☐

☐

☐

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 10A	Connector Type Field Installable
Shielded Plastic, Non-shielded	No. of Contacts 02
Connector Gender Female	Backshell Straight
Mating Style Push Lock	IP Rating IP68
Assembly Style Crimp	
More Options	

People Also Bought

- 
BB-02BFFA-QL8SPP
- 
UMN-05AMMM-...
- 
M12D04MR-12DMR-...
- 
BD-05AFFM-QL8D003
- 
HDB-15BFFA-SL7001