

Language selection: [DE](#) [EN](#)

- Welcome
- Current
- About Us
- Products
 - spacers


Metric threaded spacers



[<< previous type](#) [next guy >>](#)

Spacer bolt DIA

Stainless steel, metric thread



spacer bolts

Type 6-point
execution inside Outside
with undercut
(optional without undercut)
material Stainless steel 1.4305 / DMS 400
PU from 100 pieces
Prices all prices net per 100 pieces
distribution only to trade / industry / trade
Order example: 246 x 50 = DIA / 1.4305 / SW 7 / M4 x 50

[↑ Picture](#)

[↑ drawing](#)

[↑ info](#)

[↓ 242x](#)

[↓ external thread](#)

[↓ inner thread](#)

Order no.	SW (hexagon)	thread	05	08	10	12	15	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100
242x (length)	SW 5	M2.5	05	08	10	12	15	18	20	25	30	35	40	45	50	55	60								
244x	SW 5.5	M3	05	08	10	12	15	18	20	25	30	35	40	45	50	55	60	65	70						
246x	SW 7	M4		08	10	12	15	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100
248x	SW 8	M5			10	12	15	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100
249x	SW 10	M6			10	12	15	18	20	25	30	35	40	45	50	55	60	65	70	75	80	85	90	95	100
2413x	SW 13	M8					15		20	25	30	35	40	45	50		60		70		80		90		100