

MHDTPPK SERIES

Category:

Choose Category ▾

FEATURES

- Available in sizes 9, 15, 25 and 37-way
- Suitable for any common d-sub connector
- Strain relief inserts ensure a secure termination
- Re-openable
- Also available as a metalised (MHDTPK series) or metal (MHTZK series) version

SPECIFICATIONS

Housing Material:	ABS, Black, UL94 HB
Operating Temperature Range:	-55°C to +110°C
Cable Entry:	Top Entry
Thumbscrew:	UNC 4-40 (Standard), M2.5 or M3 (On Request)
Cable Outer Diameter	Up to 13mm



- ✓ Check Inventory
- Resource Center
- Compliance
- Custom Connectors

COOKIE POLICY

This site uses cookies and other tracking technologies to assist with navigation and your ability to provide feedback, analyse your use of our products and services. [Cookie Policy](#).

I ACCEPT

STANDARD D-SUB HOOD | TOP ENTRY

FILTER ▾

SEARCH

#	POSITION	HOUSING MATERIAL	DRAWING	ORDER SAMPLES	
	MHDTPPK-09-K	9	UL-recognised Plastic Material		
	MHDTPPK-15-K	15	UL-recognised Plastic Material		
	MHDTPPK-25-K	25	UL-recognised Plastic Material		

Have a question for MH? Connect with us. Experience makes the difference.

CONNECT

	MHDTPPK-37-K	37	UL-recognised Plastic Material		
	MHDTPPK15-DB15P-K	15	UL-recognised Plastic Material Hood		
	MHDTPPK15-DB15S-K	15	UL-recognised Plastic Material Hood		
	MHDTPPK25-DB25P-K	25	UL-recognised Plastic Material Hood	N/A	
	MHDTPPK25-DB25S-K	25	UL-recognised Plastic Material Hood	N/A	
	MHDTPPK9-DB9P-K	9	UL-recognised Plastic Material Hood	N/A	
	MHDTPPK9-DB9S-K	9	UL-recognised Plastic Material Hood	N/A	

RELATED SERIES

DTZK

IDTZK →

MHDTZK-BK →

MHDTZK-RA →

MHDTZK-RA-BK →

STOCKING DISTRIBUTORS

